



Spot of crisp white light

Twistline Alu 2000 hours

Mains-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in a superior-quality spot light. Aluminum coating prevents heat in the backlight.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Aluminum coating
- Universal burning position
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

Twistline Alu 2000 hours

Dimensional drawing

Product	D	C
Twistline Alu 2000h 25W GU10 240V 25D 1CT/50	50.7 mm	51 mm

TWIST Alu 25W GU10 240V 25D

Approval and Application	
Energy Consumption kWh/1000 h	50
Energy Efficiency Label (EEL)	D
Controls and Dimming	
Dimmable	Yes
Operating and Electrical	
Power (Rated) (Nom)	50.0
Starting Time (Nom)	0.0
Warm Up Time To 60% Light (Nom)	instant full light
General Information	
Cap-Base	GU10
Nominal Lifetime (Nom)	2000
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2800
Color Rendering Index (Nom)	100
Llmf At End Of Nominal Lifetime (Min)	80
Luminous Flux (Rated) (Nom)	330
Mechanical and Housing	
Bulb Finish	Clear (CL)

Operating and Electrical

order code	Voltage (Nom)
41258460	230
42856160	240
42850960	240

General Information

order code	Bulb Shape	Philips Code
41258460	MR16	18044
42856160	MR16	18045

order code	Bulb Shape	Philips Code
42850960	-	NA

Light Technical

order code	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
41258460	40	600	40
42856160	40	600	40

order code	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
42850960	20	1000	20

Twistline Alu 2000 hours

