



Brighten your home with infinite possibilities

DuraMax Deco Globe

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

Benefits

- Philips DuraMax long life deco globe bulbs last longer than standard incandescent, significantly reducing the hassle of replacing light bulbs that burn out too quickly.
- Philips DuraMax decorative globe bulbs add a pleasant touch to home décor.

Features

- Lasts at Least Two years!*
- Available in a variety of wattages.
- Medium and Candelabra bases.
- White finish adds a soft white glow, Clear finish adds decorative sparkle and half-chrome provides decorative sparkle and reduced glare.
- Available in: G16.5 medium white: 25 and 40 watt; G30: 60 and 100 watt; G16.5 medium clear and G40 clear: 40 and 60 watt; G25 half-chrome: 40 watt; G40 white: 40, 60, 100, 150 watt; G25 clear and G16.5 white and clear cand.: 25, 40, 60 watt; G25 white: 25, 40, 60, 100 watt.
- *Based on an average of hours usage per day/7 days per week. Hours differ between products, and there are exceptions. See individual products for details.

DuraMax Deco Globe

Application

• For general or ambient lighting in vanity strips, pendant and hanging light fixtures.

Versions



E26, G16 1/2, Clear



E12, G16 1/2, Clear



E26, G40, Clear



E26, G40, White




E26, G25, Clear



E26, G25, White

Dimensional drawing



Product




BC40G16-1/2C/CL/LL 120V 6/2TP

BC25G16-1/2C/CL/LL 120V

BC60G16-1/2C/CL/LL 120V 6/2TP

DuraMax Deco Globe

Dimensional drawing



Product
40G25/CL/LL 120V 4/3
40G25/CL/LL 120V 12/1 TP
40G25/W/LL 120V 4/3
40G25/W/LL 120V 12/1 TP
25G25/W/LL 120V 12/1 TP
25G25/CL/LL 120V 12/1 TP

Product
60G40/W/LL 6/1 TP
60G40/CL/LL 120V 6/1 TP

Product
BC40G16-1/2/CL/LL 120V 6/2 TP

Operating and Electrical	
Voltage (Nom)	120 V

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
135376	BC40G16-1/2/CL/LL 120V 6/2 TP	40 W
166990	BC60G16-1/2C/CL/LL 120V 6/2TP	60 W
168450	BC25G16-1/2C/CL/LL 120V 6/2	25 W
168468	BC40G16-1/2C/CL/LL 120V 6/2TP	40 W
168526	60G40/CL/LL 120V 6/1 TP	60 W
168518	60G40/W/LL 6/1 TP	60 W

Order Code	Full Product Name	Power (Rated) (Nom)
168872	25G25/CL/LL 120V 12/1 TP	25 W
167478	40G25/CL/LL 120V 12/1 TP	40 W
169037	40G25/CL/LL 120V 4/3	40 W
167486	25G25/W/LL 120V 12/1 TP	25 W
167460	40G25/W/LL 120V 12/1 TP	40 W
169045	40G25/W/LL 120V 4/3	40 W

General Information

DuraMax Deco Globe

Order Code	Full Product Name	Cap-Base	Main Application	Operating Position	Rated Lifetime (Hours)
135376	BC40G16-1/2/CL/LL 120V 6/2 TP	E26	Decorative	Base Down +/- 90 D	2000 h
166990	BC60G16-1/2C/CL/LL 120V 6/2TP	E12	Decorative	Base Down +/- 90 D	2000 h
168450	BC25G16-1/2C/CL/LL 120V 6/2	E12	Decorative	Base Down +/- 90 D	2000 h
168468	BC40G16-1/2C/CL/LL 120V 6/2TP	E12	Decorative	Base Down +/- 90 D	2000 h
168526	60G40/CL/LL 120V 6/1 TP	E26	Decorative	Universal	3000 h
168518	60G40/W/LL 6/1 TP	E26	Decorative	Universal	3000 h

Order Code	Full Product Name	Cap-Base	Main Application	Operating Position	Rated Lifetime (Hours)
168872	25G25/CL/LL 120V 12/1 TP	E26	Vanity	Universal	2000 h
167478	40G25/CL/LL 120V 12/1 TP	E26	Vanity	Universal	1500 h
169037	40G25/CL/LL 120V 4/3	E26	Vanity	Universal	1500 h
167486	25G25/W/LL 120V 12/1 TP	E26	Vanity	Universal	2000 h
167460	40G25/W/LL 120V 12/1 TP	E26	Vanity	Universal	1500 h
169045	40G25/W/LL 120V 4/3	E26	Vanity	Universal	1500 h

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
135376	BC40G16-1/2/CL/LL 120V 6/2 TP	390 lm
166990	BC60G16-1/2C/CL/LL 120V 6/2TP	540 lm
168450	BC25G16-1/2C/CL/LL 120V 6/2	200 lm
168468	BC40G16-1/2C/CL/LL 120V 6/2TP	300 lm
168526	60G40/CL/LL 120V 6/1 TP	665 lm
168518	60G40/W/LL 6/1 TP	595 lm

Order Code	Full Product Name	Luminous Flux (Nom)
168872	25G25/CL/LL 120V 12/1 TP	235 lm
167478	40G25/CL/LL 120V 12/1 TP	410 lm
169037	40G25/CL/LL 120V 4/3	410 lm
167486	25G25/W/LL 120V 12/1 TP	210 lm
167460	40G25/W/LL 120V 12/1 TP	370 lm
169045	40G25/W/LL 120V 4/3	370 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
135376	BC40G16-1/2/CL/LL 120V 6/2 TP	Clear (CL)	G-16 1/2
166990	BC60G16-1/2C/CL/LL 120V 6/2TP	Clear (CL)	G-16 1/2
168450	BC25G16-1/2C/CL/LL 120V 6/2	Clear (CL)	G-16 1/2
168468	BC40G16-1/2C/CL/LL 120V 6/2TP	Clear (CL)	G-16 1/2
168526	60G40/CL/LL 120V 6/1 TP	Clear (CL)	G40
168518	60G40/W/LL 6/1 TP	White (WH)	G40

Order Code	Full Product Name	Bulb Finish	Bulb Shape
168872	25G25/CL/LL 120V 12/1 TP	Clear (CL)	G25
167478	40G25/CL/LL 120V 12/1 TP	Clear (CL)	G25
169037	40G25/CL/LL 120V 4/3	Clear (CL)	G25
167486	25G25/W/LL 120V 12/1 TP	White (WH)	G25
167460	40G25/W/LL 120V 12/1 TP	White (WH)	G25
169045	40G25/W/LL 120V 4/3	White (WH)	G25

