



Brighten your home with infinite possibilities

DuraMax Deco Globe

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. DuraMax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

Benefits

- Philips DuraMax long life deco globe bulbs last longer than standard incandescent, significantly reducing the hassle of replacing light bulbs that burn out too quickly.
- Philips DuraMax decorative globe bulbs add a pleasant touch to home décor.

Features

- Lasts at Least Two years!*
- Available in a variety of wattages.
- Medium and Candelabra bases.
- White finish adds a soft white glow, Clear finish adds decorative sparkle and half-chrome provides decorative sparkle and reduced glare.
- Available in: G16.5 medium white: 25 and 40 watt; G30: 60 and 100 watt; G16.5 medium clear and G40 clear: 40 and 60 watt; G25 half-chrome: 40 watt; G40 white: 40, 60, 100, 150 watt; G25 clear and G16.5 white and clear cand.: 25, 40, 60 watt; G25 white: 25, 40, 60, 100 watt.
- *Based on an average of hours usage per day/7 days per week. Hours differ between products, and there are exceptions. See individual products for details.

DuraMax Deco Globe

Application

- For general or ambient lighting in vanity strips, pendant and hanging light fixtures.

Versions



LPPR I-G25 CL



LPPR I-G25 WH





LPPR I-G16Hlf ES WH



LPPR I-G16Hlf ES CL

Dimensional drawing



Product

BC40G16-1/2/CL/LL 120V 6/2 TP


BC40G16/D/W 6/2PK

Product

BC40G16-1/2C/CL/LL 120V 6/2TP

BC60G16-1/2C/CL/LL 120V 6/2TP

Dimensional drawing



Operating and Electrical	
Voltage (Nom)	120 V

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Operating Position
925178136304	BC60G16-1/2C/CL/LL 120V 6/2TP	E12	2,000 hour(s)	S90
925261636308	BC40G16-1/2C/CL/LL 120V 6/2TP	E12	2,000 hour(s)	S90
925186636323	25G25/CL/LL 120V 12/1 TP	E26	2,000 hour(s)	UNIVERSAL

Light Technical

Order Code	Full Product Name	Luminous Flux
925178136304	BC60G16-1/2C/CL/LL 120V 6/2TP	540 lm
925261636308	BC40G16-1/2C/CL/LL 120V 6/2TP	300 lm
925186636323	25G25/CL/LL 120V 12/1 TP	235 lm
925244136345	40G25/CL/LL 120V 12/1 TP	410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
925178136304	BC60G16-1/2C/CL/LL 120V 6/2TP	60 W
925261636308	BC40G16-1/2C/CL/LL 120V 6/2TP	40 W
925186636323	25G25/CL/LL 120V 12/1 TP	25 W
925244136345	40G25/CL/LL 120V 12/1 TP	40 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925178136304	BC60G16-1/2C/CL/LL 120V 6/2TP	Clear	G16.5
925261636308	BC40G16-1/2C/CL/LL 120V 6/2TP	Clear	G16.5
925186636323	25G25/CL/LL 120V 12/1 TP	Clear	G25
925244136345	40G25/CL/LL 120V 12/1 TP	Clear	G25

Product
25G25/CL/LL 120V 12/1 TP
40G25/CL/LL 120V 12/1 TP
40G25/W/LL 120V 12/1 TP

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Operating Position
925244136345	40G25/CL/LL 120V 12/1 TP	E26	1,500 hour(s)	UNIVERSAL
925244036357	40G25/W/LL 120V 12/1 TP	E26	1,500 hour(s)	UNIVERSAL
925168536301	BC40G16/D/W 6/2PK	E26	2,000 hour(s)	UNIVERSAL
925171036303	BC40G16-1/2/CL/LL 120V 6/2 TP	E26	2,000 hour(s)	S90

Order Code	Full Product Name	Luminous Flux
925244036357	40G25/W/LL 120V 12/1 TP	370 lm
925168536301	BC40G16/D/W 6/2PK	228 lm
925171036303	BC40G16-1/2/CL/LL 120V 6/2 TP	390 lm

Order Code	Full Product Name	Power Consumption
925244036357	40G25/W/LL 120V 12/1 TP	40 W
925168536301	BC40G16/D/W 6/2PK	40 W
925171036303	BC40G16-1/2/CL/LL 120V 6/2 TP	40 W

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925244036357	40G25/W/LL 120V 12/1 TP	White	G25
925168536301	BC40G16/D/W 6/2PK	White	G16.5
925171036303	BC40G16-1/2/CL/LL 120V 6/2 TP	Clear	G16.5

