



Reflector Agro

Reflector Agro

Philips Family of Reflector Agro provide the perfect light to promote plant growth.

Features

- Promotes plant growth by producing the appropriate light spectrum for plants to thrive.
- Available in: R20: 50 watt; BR30: 75 watt; and BR40:150 watt.

Application

- Ideal for indoor recessed, track, and portable fixtures.


Versions



Single Contact Medium Screw
BR-30 (BR30) Agro Blue

Reflector Agro

Dimensional drawing



Product

75BR30/AGRO 120V

