



Reflector Flood

Reflector Flood

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

Features

- For parties, holiday lighting and decorative effects.
- Available in BR, R and PAR shapes in 45W, 50W, 65W, 85W, 120W and 300W versions.

Application

- Ideal for indoor recessed and track fixtures and outdoor landscape fixtures.


Versions



Single Contact Medium Screw
BR40 Frosted

Reflector Flood

Dimensional drawing



Product

65BR30/FL55 CDA 130V

