



# Silicone Coated Rough Service

## Silicone Coated Rough Service

The Philips Family of Silicone Coated Rough Service bulbs are the perfect choice in areas where there is concern if a bulb drops or shatters. Since Silicone Coated Rough Service bulbs resist breakage or shattering, they are perfect for food serving areas, as well as, standard, industrial rough surface, appliance and sign use.

### Benefits

- Resists breakage or shattering if bulb is hit or dropped.
- Absorbs Impact.
- Resists Moisture.

### Features

- Special Silicone Coating.
- Repels Machine Splatter- without breakage caused by thermal shock.
- Available in: A19: 50 watt; A21: 75 watt; PS30: 200 watt.

### Application

- Ideal for factory lighting, new construction, food serving areas, refrigerators, garden fountains and drop cords.

# Silicone Coated Rough Service

## Versions



A21,E26

## Dimensional drawing



Product
100A/RS/TF 120-130V 60PK

