



Rough Service Incandescent Lamps

Rough / Vibration Service

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Benefits

- An exceptionally strong filament resists shocks, bumps and vibrations.

Features

- Rugged design resists vibration.
- Incandescent, vacuum or gas-filled lamp with clear or inside-frosted bulb.
- Single coil filament.
- Medium or mogul screw base.
- Available in 60W and 75W versions in clear and frosted. Also available in 100W TuffGuard version.

Application


- Ideal for use in worklights and other fixtures subject to rough handling. Suited for Ships, engine rooms, mines, elevators public transport buses and trains and other industrial applications.

Versions



Single Contact Medium Screw A
19mm Frosted

Dimensional drawing



A19

Product	D	C (max)
50A/2P/RS 12/2 PK	2.375 in	4.438 in
100A/2P/RS 12/2	2.375 in	4.438 in



Rough / Vibration Service

Operating and electrical	
Voltage (Nom)	130 V
General information	
Cap-Base	E26
Main Application	General Lighting (G)
Operating Position	Universal
Rated Lifetime (Hours)	2000 h
Mechanical and housing	
Bulb Finish	Frosted
Bulb Shape	A19 (A19)

Operating and electrical

Order Code	Full Product Name	Power (Nom)
111716	50A/2P/RS 12/2 PK	50 W

Order Code	Full Product Name	Power (Nom)
111724	100A/2P/RS 12/2	100 W

