



# Lamp:

## Standard Candle B35 frosted

Flame-shaped bulb with clear or inside-frosted glass and vacuum- or gas-filled bulb

### Benefits

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

### Features

- Clear lamps:
  - slender, crystal-clear lamps designed for sparkling highlights
  - creates a classic sparkling atmosphere
- Frosted lamps:
  - slender, frosted lamps
  - creates a low-glare atmosphere
- Universal burning position except for some 60W types which must be operated vertically, base-down (tolerance 90°)

### Application


- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 frosted

Versions



Dimensional drawing



| Product                                     | D     | C (max) |
|---|-------|---------|
| Standard 25W E14 220-240V B35 FR 1CT/10X10F | 35 mm | 100 mm  |

