



Product Description

Standard Extra Low Voltage A60

Clear lamp (A-bulb) for operation on voltages of 24 and 50V

Benefits

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

Features

- Types till 42V are safer in combination with a mains power supply transformer

Application


- Rural and isolated areas where mains power supplies are not available
- Emergency lighting installations

Versions



Standard Extra Low Voltage A60

Dimensional drawing



Product	D (max)	C (max)
Standard ELV 40W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm
Standard ELV 40W E27/BRC 24V A60 CL 1CT	60 mm	107.5 mm
Standard ELV 60W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm

Approval and Application

Energy Efficiency Label (EEL)	D
-------------------------------	---

Controls and Dimming

Dimmable	yes
----------	-----

Operating and Electrical

Starting Time (Nom)	0.0 s
---------------------	-------

Warm Up Time To 60% Light (Nom)	instant full light
---------------------------------	--------------------

General Information

Cap-Base	E27
----------	-----

Nominal Lifetime (Nom)	1000 h
------------------------	--------

Operating Position	UNIVERSAL
--------------------	-----------

Rated Lifetime (Hours)	1000 h
------------------------	--------

Switching Cycle	4000X
-----------------	-------

Light Technical

Correlated Colour Temperature (Nom)	2700 K
-------------------------------------	--------

Colour Rendering Index (Nom)	100
------------------------------	-----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Bulb Shape	A60
------------	-----

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
02293684	STAN ELV 40W E27/BRC 24V A60 CL 1CT	40 kWh
10156384	STAN ELV 40W E27/BRC 50V A60 CL 1CT	40 kWh
10188484	STAN ELV 60W E27/BRC 50V A60 CL 1CT	60 kWh

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
02293684	STAN ELV 40W E27/BRC 24V A60 CL 1CT	24 V	40 W
10156384	STAN ELV 40W E27/BRC 50V A60 CL 1CT	50 V	40.0 W

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
10188484	STAN ELV 60W E27/BRC 50V A60 CL 1CT	50 V	60.0 W

Light Technical

Standard Extra Low Voltage A60

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
02293684	STAN ELV 40W E27/BRC 24V A60 CL 1CT	580 lm	580 lm
10156384	STAN ELV 40W E27/BRC 50V A60 CL 1CT	520 lm	520 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
10188484	STAN ELV 60W E27/BRC 50V A60 CL 1CT	810 lm	810 lm

