



Product Description

Standard Extra Low Voltage A60

Clear lamp (A-bulb) for operation on voltages of 24 and 50V

Benefits

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

Features

- Types till 42V are safer in combination with a mains power supply transformer

Application


- Rural and isolated areas where mains power supplies are not available
- Emergency lighting installations

Versions



Standard Extra Low Voltage A60

Dimensional drawing



Product	D (max)	C (max)
Stan ELV 40W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm

