



# Lampe :

## Standard Très bas voltage

Lampe claire pour tensions 24V

### Avantages

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

### Fonctions

- Toutes positions de fonctionnement

### Application

- Zones rurales et isolées ne disposant pas de la tension d'alimentation secteur
- Installations d'éclairage d'urgence