

Digital ignitors for maximum reliability

HID ignitors for series systems

HID ignitors for series systems

Benefits

- Easy installation and wiring
- Can operate with both semi-parallel and series ballasts
- Digital ignitors ensure maximum reliability

Features

- Ignitors equipped with screw terminal blocks as standard
- Series ignitor will only work in series circuits

Application

- Outdoor lighting (most popular application: road and tunnel lighting)


Versions



SN 59 220-240V 50/60Hz

HID ignitors for series systems

Dimensional drawing



Product	D1	C1	A1	A2	B1
SN 59 220-240V 50/60Hz	4.3 mm	38.0 mm	114.5 mm	95.0 mm	41.0 mm

