



# Digital ignitors for maximum reliability

## HID ignitors for series systems

### HID ignitors for series systems

## Benefits

- Easy installation and wiring
- Can operate with both semi-parallel and series ballasts
- Digital ignitors ensure maximum reliability

## Features

- Ignitors equipped with screw terminal blocks as standard
- Series ignitor will only work in series circuits

## Application


- Outdoor lighting (most popular application: road and tunnel lighting)

## Versions



HID ignitors for series systems

Dimensional drawing



Product	D1	C1	A1	A2	B1
SND 58 220-240V 50/60Hz	4.3 mm	38.5 mm	84.5 mm	65.0 mm	41.5 mm

