



Product Description

Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

Features

- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas


Standard Lustre P45 frosted

Versions



LPPR ILUSESTD E27 P45 CL

Dimensional drawing



Product	D	C (max)
Stan 40W E27 220-240V P45 FR 1CT/5X10F	45 mm	73 mm

