



Product Description

Appliance Oven P45

Lustre vacuum lamps with clear glass (P-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight


Versions



LPPR ITUBAPE 0001

Appliance Oven P45

Dimensional drawing



Product	D	C (max)
Appl 40W E14 240V P45 CL OV 1BL/10	45 mm	75 mm

