



Sumo electronic ballast for TL-D/TL5 lamps

Sumo Electronic ballast for TL5/TL-D lamps (India)

Compact, lightweight, high-frequency electronic ballasts for TL-D/TL5 fluorescent lamps

Benefits

- More than 25% reduction in energy consumption compared with conventional electromagnetic ballasts at equal luminous flux
- No blackening of walls

Features

- Flicker-free instant start
- Minimum ignition voltage of 90 V
- Footprint (fixing holes) matches conventional electromagnetic potted ballast

Application


- Home
- Retail
- Areas with acute low-voltage problems

Sumo Electronic ballast for TL5/TL-D lamps (India)

Versions



Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|----------------|--------|---------|----------|----------|---------|
| Sumo ultra 136 | 4.0 mm | 27.0 mm | 136.0 mm | 130.0 mm | 40.0 mm |

