

# EB-T electronic ballasts for TL5 lamps

## EB-T Electronic ballasts for TL5 lamps (India)

Slim, lightweight, high-frequency electronic ballasts for TL5 lamps

### Benefits

- Up to 25% reduction in energy consumption compared with conventional gear at constant luminous flux
- Compared with TL-D lamps, TL5 can reduce the number of light points by 10% in a new installation
- Over 40% saving on energy consumption in air-conditioned spaces thanks to reduced heat load on compressor

### Features

- Flicker-free warm start ensures long lamp life
- Unit is protected against excessive mains voltages and incorrect connection. Complete shutdown at mains voltages exceeding 300 V AC. Restarts after reset and switching on.
- End-of-life protection

### Application

- Areas with long hours of usage, e.g. industrial premises, airports and railway stations
- Retail and hospitality
- Office buildings and hospitals


# EB-T Electronic ballasts for TL5 lamps (India)

## Versions



EB-T 128 TL5 220-240V 50/60 Hz

## Dimensional drawing



Product	D1	C1	A1	A2	B1
EBT 228 TL5 240	4.2 mm	29.0 mm	258.0 mm	244.0 mm	30.0 mm

