



Product Description

PAR38 Colours

Coloured pressed-glass 121 mm diameter reflector lamp

Benefits

- Gives striking decorative effects, both indoors and outdoors
- 20% lower power consumption compared with conventional coloured PAR lamps

Features

- Weatherproof coloured coating on the refractor face in a choice of colours
- Flood beam width

Application


- Parks, public and private gardens
- Festive illumination
- Restaurants, bars, dance halls, discotheques
- Show-window displays, fountains and 'Son et Lumi' spectacles
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder

PAR38 Colours

Versions



Dimensional drawing



Product	D (max)	C (max)
PAR38 Colours 80W E27 230V GR 1CT/12	123 mm	137 mm

