



Product Description

PAR56

Extremely powerful pressed-glass 179 mm diameter reflector lamps

Οφέλη

- For indoor and outdoor use wherever high illuminance levels are required

Χαρακτηριστικά

- Made of heat-resistant glass
- Special sturdy, shock-resistant 12V version available for underwater applications
- 12V lamp has screw terminals for secure connection because of the high running current (25A)

Εφαρμογή


- Spot versions are designed for long-distance beaming
- Flood and Wide Flood versions are mainly used for high mounting applications
- Displays, museums, public and commercial buildings, towers, churches, high-roofed halls, sports halls, garden lighting, exhibitions
- PAR56 Underwater: swimming pools and fountains, or wherever extra-low-voltage lamps are required for safety

PAR56

Versions




Σχεδιάγραμμα διαστάσεων




Product	D (max)	C (max)	C1
PAR56 300W GX16d 230V WFL 1CT/6	178.5 mm	126.9 mm	98 mm

Light Distribution Diagrams



Accent Diagrams



Beam Diagrams

