



## Product Description

### Reflector diam 39 mm

Reflector lamps based on advanced spotlighting technology

#### Benefits

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

#### Features

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- R39 flood is the smallest model in the range
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile

#### Application

- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes


#### Versions



E14, R39

Reflector diam 39 mm

Dimensional drawing



Product	D	C (max)
STD 30W 240V R39 E14 FR 1CT/12	39 mm	67 mm

