



Product Description

Reflector diam 63 mm

Reflector lamps based on advanced spotlighting technology

Benefits

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

Features

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile

Application


- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

Versions




Reflector diam 63 mm

Dimensional drawing




Product	D
Reflector 60W E27 240V NR63 30D FR 1CT/6X5F	63 mm

Light Distribution Diagrams



Accent Diagrams



Reflector diam 63 mm

Beam Diagrams

