



# Product Description

## Reflector diam 63 mm

Reflector lamps based on advanced spotlighting technology

### Benefits

- Centre-beam intensities up to 100% higher than with conventional reflector lamps


### Features

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile

### Application

- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

### Dimensional drawing




Product	D
Refl 40W E27 230V NR63 30D 1CT/30	63 mm
Refl 60W E27 230V NR63 30D FR 1CT/30	63 mm

Reflector diam 63 mm


General Information	
Cap-Base	E27
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63

Operating and Electrical

Order Code	Full Product Name	Power Consumption
04366578	Reflector 60W E27 230V NR63 30D FR 1CT/30	60 W
04360378	REFL 40W E27 230V NR63 30D 1CT/30	40 W




Accent Diagrams



Accent Diagram - Refl 60W E27 230V NR63 30D  
FR 1CT/30

Reflector diam 63 mm

Beam Diagrams



Beam diagram - Refl 60W E27 230V NR63 30D  
FR 1CT/30

