



Product Description

Reflector diam 63 mm

Reflector lamps based on advanced spotlighting technology

Benefits

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

Features

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile

Application


- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

Versions




Reflector diam 63 mm


Dimensional drawing



Product	D
Refl 60W E27 230V NR63 30D FR 1CT/30	63 mm




Accent Diagrams



Accent Diagram - Refl 60W E27 230V NR63 30D
FR 1CT/30

Beam Diagrams



Beam diagram - Refl 60W E27 230V NR63 30D
FR 1CT/30

Reflector diam 63 mm

