



Product Description

Reflector diam 63 mm

Reflector lamps based on advanced spotlighting technology

Benefits

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

Features

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile

Application


- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

Versions



Reflector diam 63 mm

Dimensional drawing




Product	D
REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F	63 mm
Refl 40W E27 230V NR63 30D 1CT/30	63 mm
Refl 60W E27 230V NR63 30D FR 1CT/30	63 mm

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63


Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
923339445558	REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F	240 V	60 W
926000005918	Refl 60W E27 230V NR63 30D FR 1CT/30	230 V	60 W
926000006213	Refl 40W E27 230V NR63 30D 1CT/30	230 V	40 W




Reflector diam 63 mm

Accent Diagrams



Accent Diagram - REF SPOT 60W E27 240V
NR63 30DFR2CT/4X3F

Beam Diagrams



Beam diagram - REF SPOT 60W E27 240V
NR63 30DFR2CT/4X3F

