



Product Description

Reflektorové R63

Reflector lamps based on advanced spotlighting technology

Výhody

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

Vlastnosti

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile

Aplikácie


- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

Versions




Reflektorové R63


Rozmerový obrázok



Product	D
Reflector 60W E27 230V NR63 30D FR 1CT/30	63 mm




Accent Diagrams



LDAC_IREFESP_60W_NR63_30D-Accent diagram

Beam Diagrams



LDBE_IREFESP_60W_NR63_30D-Beam diagram

Reflektorové R63

