



Product Description

Standard A-shape frosted

Conventional pear-shaped incandescent lamps

Benefits

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of pearl lamp
- Universal burning position


Features

- Vacuum-filled (15W) or gas-filled (25W and above)

Application

- Frosted lamps give low glare and diffused lighting for universal applicability

Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 230V A55 FR 1CT/12X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 FR 1CT/12X10F	56 mm	55 mm	97 mm
Stan 75W E27 230V A55 FR 1CT/12X10F	56 mm	55 mm	97 mm

Standard A-shape frosted

General Information	
Cap-Base	E27
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55

General Information

Order Code	Full Product Name	Rated Lifetime (Hours)
35474784	STAN 75W E27 230V A55 FR 1CT/12X10F	1,000 hour(s)
35471684	STAN 60W E27 230V A55 FR 1CT/12X10F	1,000 hour(s)
35477884	STAN 100W E27 230V A55 FR 1CT/12X10F	-

Light Technical

Order Code	Full Product Name	Luminous Flux
35474784	STAN 75W E27 230V A55 FR 1CT/12X10F	930 lm
35471684	STAN 60W E27 230V A55 FR 1CT/12X10F	710 lm

Order Code	Full Product Name	Luminous Flux
35477884	STAN 100W E27 230V A55 FR 1CT/12X10F	1,340 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
35474784	STAN 75W E27 230V A55 FR 1CT/12X10F	75 W
35471684	STAN 60W E27 230V A55 FR 1CT/12X10F	60 W

Order Code	Full Product Name	Power Consumption
35477884	STAN 100W E27 230V A55 FR 1CT/12X10F	100 W

