



# Product Description

## Standard A-shape clear

Conventional pear-shaped incandescent lamps

### Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect
- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect


### Features

- Vacuum-filled (15W) or gas-filled (25W and above)
- Vacuum-filled (15W) or gas-filled (25W and above)

### Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare
- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare

## Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm
Stan 60W E27 240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm
Stan 75W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm

# Standard A-shape clear

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

## Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)
920054645597	Stan 60W E27 240V A55 CL 1CT/10X10F	240 V
926000004004	Stan 75W E27 230V A55 CL 1CT/12X10F	230 V

Order Code	Full Product Name	Voltage (Nom)
926000004009	Stan 100W E27 240V A55 CL 1CT/10X10F	240 V

