



# Product Description

## Deco Tubular

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

### Benefits

- Give brilliant and decorative lighting effects
- Ideal for creating a comfortable and relaxing ambience

### Features

- Internal coating cannot chip, fade, become scratched or weathered

### Application



- General lighting: switchboards, cupboards, piano and painting lighting
- Clear lamps are suitable for use in industrial and professional lighting applications, such as sign boards, elevator sign systems and fair and festive lighting
- Lamps with inside-frosted bulbs are ideal for use in a wide range of domestic and industrial applications

### Versions



## Deco Tubular

### Dimensional drawing



Product	D	C (max)
40W E14 240V T25L CL CH 1CT/10x10F	25 mm	81 mm

Product	D (max)	C (max)
Deco 10W E14 240-250V T17 CL 1CT/10X10F	17 mm	54 mm
Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	17 mm	54 mm

#### General Information

Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL

#### Operating and Electrical

Starting Time (Nom)	0.0 s
---------------------	-------

#### Mechanical and Housing

Bulb Finish	Clear
-------------	-------

### General Information

Order Code	Full Product Name	Switching Cycle
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-
924151144441	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	4,000

Order Code	Full Product Name	Switching Cycle
924151445740	Deco 10W E14 240-250V T17 CL 1CT/10X10F	4,000

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-	-	424 lm
924151144441	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	2700 K	100	21 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
924151445740	Deco 10W E14 240-250V T17 CL 1CT/10X10F	2700 K	100	37 lm

Operating and Electrical

Order Code	Full Product	Warm-up	Lamp	Voltage (Nom)	Power Consumption
	Name	time to 60% light	Current (Nom)		
925350444480	40W E14 240V T25L CL CH 1CT/ 10x10F	-	-	230-240 V	40 W
924151144441	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	instant full light s	0.03 A	230-240 V	7 W

Order Code	Full Product	Warm-up	Lamp	Voltage (Nom)	Power Consumption
	Name	time to 60% light	Current (Nom)		
924151445740	Deco 10W E14 240-250V T17 CL 1CT/10X10F	instant full light s	-	240-250 V	10.0 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-
924151144441	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	Yes

Order Code	Full Product Name	Dimmable
924151445740	Deco 10W E14 240-250V T17 CL 1CT/10X10F	Yes

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	T25
924151144441	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	T17

Order Code	Full Product Name	Bulb Shape
924151445740	Deco 10W E14 240-250V T17 CL 1CT/10X10F	T17

Approval and Application

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-
924151144441	Deco 7.0W E14 230-240V T17 CL 1CT/ 10X10F	7 kWh

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
924151445740	Deco 10W E14 240-250V T17 CL 1CT/10X10F	10 kWh

