



Product Description

Σωληνωτοί Φούρνου Μικροκυμάτων

Tubular vacuum lamp with clear bulb

Οφέλη

- Reinforced filament construction for resistance to vibration
- Easy mounting with various fixing parts allows the lamps to be used in the area in the oven where light is needed
- Long useful life in microwave ovens

Χαρακτηριστικά

- Reinforced single / double coil filament
- T-CLICK design specially developed for use in microwave ovens

Εφαρμογή

- Microwave ovens

Versions



E14

Σωληνωτοί Φούρνου Μικροκυμάτων

Σχεδιάγραμμα διαστάσεων

Product	D (max)	C (max)
Appliance 25W E14 230~240V T25 CL MWO 1BL/10	25 mm	57 mm

