



Product Description

Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)


Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight


Dimensional drawing



Product	D (max)	C (max)
Appliance 15W E14 230-240V T22 CL OV 1CT	7/8 in	1-15/16 in

Appliance Oven Tubular

Dimensional drawing



Product	D (max)	C (max)
Appliance 25W E14 230-240V T25 CL OV 1CT	1 in	2-1/4 in

Controls and dimming	
Dimmable	Yes
Operating and electrical	
Voltage (Nom)	230-240 V
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light
General information	
Cap-Base	E14
Nominal Lifetime (Nom)	1000 h
Main Application	Oven
Operating Position	Universal
Rated Lifetime (Hours)	1000 h
Rated Lifetime (Years)	1 a
Switching Cycle	4000X
Light technical	
Chromaticity Coordinate X (Nom)	0.46
Chromaticity Coordinate Y (Nom)	0.411
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	100
Mechanical and housing	
Bulb Finish	Clear

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
250803	APP 15W E14 230-240V T22 CL OV 1CT	16 kWh
250811	APP 25W E14 230-240V T25 CL OV 1CT	26 kWh

Operating and electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
250803	APP 15W E14 230-240V T22 CL OV 1CT	0.06 A	15.4 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
250811	APP 25W E14 230-240V T25 CL OV 1CT	0.11 A	26 W

Light technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
250803	APP 15W E14 230-240V T22 CL OV 1CT	85 lm	90 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
250811	APP 25W E14 230-240V T25 CL OV 1CT	165 lm	172 lm

Appliance Oven Tubular

Mechanical and housing

Order Code	Full Product Name	Bulb Shape
250803	APP 15W E14 230-240V T22 CL OV 1CT	T6

Order Code	Full Product Name	Bulb Shape
250811	APP 25W E14 230-240V T25 CL OV 1CT	T-7

