



# Product Description

## Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

### Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

### Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

### Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

### Versions





E14, T22, Clear



E14, T25, Clear

# Appliance Oven Tubular

## Dimensional drawing



Product	D (max)	C (max)
Appliance 15W E14 230-240V T22 OV 1CT/10x10F	22 mm	49 mm
Appliance 15W E14 230-240V T22 CL OV 1BS/10	22 mm	49 mm
Appliance 15W E14 230-240V T22 CL OV 2BL/10	22 mm	49 mm
Appliance 15W E14 230-240V T22 CL OV 1BL/10	22 mm	49 mm
Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO	22 mm	49 mm
Appliance 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm
Appliance 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

Product	D (max)	C (max)
Appliance 25W E14 230-240V T25 OV 1CT/10x10F	25 mm	57 mm
Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	25 mm	57 mm
Appliance 25W E14 230-240V T25 CL OV 1CT	25 mm	57 mm
Appliance 25W E14 230-240V T25 CL OV 1CT	25 mm	57 mm

### Approval and Application

Energy Efficiency Label (EEL)	E
-------------------------------	---

### Controls and Dimming

Dimmable	Yes
----------	-----

### Operating and Electrical

Voltage (Nom)	230-240 V
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light

### General Information

Cap-Base	E14
Nominal Lifetime (Nom)	1000 h
Main Application	Oven
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	1000 h
Switching Cycle	4000X

### Light Technical

Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	100

### Mechanical and Housing

Bulb Finish	Clear
-------------	-------

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
921096244427	Appliance 15W E14 230-240V T22 CL OV 1CT	15 kWh
924196244402	Appliance 15W E14 230-240V T22 OV 1CT/10x10F	15 kWh
924196244440	Appliance 15W E14 230-240V T22 CL OV 1CT	15 kWh
924196244442	Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO	15 kWh
924196244451	Appliance 15W E14 230-240V T22 CL OV 1BL/10	15 kWh
924196244452	Appliance 15W E14 230-240V T22 CL OV 2BL/10	15 kWh
924196244453	Appliance 15W E14 230-240V T22 CL OV 1BS/10	15 kWh
921098244433	Appliance 25W E14 230-240V T25 CL OV 1CT	25 kWh
924198244403	Appliance 25W E14 230-240V T25 OV 1CT/10x10F	25 kWh
924198244440	Appliance 25W E14 230-240V T25 CL OV 1CT	25 kWh
924198244442	Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	25 kWh

## Operating and Electrical

## Appliance Oven Tubular

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Max)	Power (Rated) (Min)	Power (Rated) (Nom)
921096244427	Appliance 15W E14 230-240V T22 CL OV 1CT	0.06 A	-	-	15.0 W
924196244402	Appliance 15W E14 230-240V T22 OV 1CT/10x10F	0.06 A	-	-	15.0 W
924196244440	Appliance 15W E14 230-240V T22 CL OV 1CT	0.06 A	-	-	15.0 W
924196244442	Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO	0.06 A	-	-	15.0 W
924196244451	Appliance 15W E14 230-240V T22 CL OV 1BL/10	0.06 A	-	-	15.0 W
924196244452	Appliance 15W E14 230-240V T22 CL OV 2BL/10	0.06 A	-	-	15.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Max)	Power (Rated) (Min)	Power (Rated) (Nom)
924196244453	Appliance 15W E14 230-240V T22 CL OV 1BS/10	0.06 A	-	-	15.0 W
921098244433	Appliance 25W E14 230-240V T25 CL OV 1CT	0.11 A	-	-	25.0 W
924198244403	Appliance 25W E14 230-240V T25 OV 1CT/10x10F	0.11 A	- W	- W	25.0 W
924198244440	Appliance 25W E14 230-240V T25 CL OV 1CT	0.11 A	-	-	25.0 W
924198244442	Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	0.11 A	-	-	25.0 W

### Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
921096244427	Appliance 15W E14 230-240V T22 CL OV 1CT	90 lm	90 lm
924196244402	Appliance 15W E14 230-240V T22 OV 1CT/10x10F	90 lm	90 lm
924196244440	Appliance 15W E14 230-240V T22 CL OV 1CT	90 lm	90 lm
924196244442	Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO	90 lm	90 lm
924196244451	Appliance 15W E14 230-240V T22 CL OV 1BL/10	90 lm	90 lm
924196244452	Appliance 15W E14 230-240V T22 CL OV 2BL/10	90 lm	90 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
924196244453	Appliance 15W E14 230-240V T22 CL OV 1BS/10	90 lm	90 lm
921098244433	Appliance 25W E14 230-240V T25 CL OV 1CT	172 lm	172 lm
924198244403	Appliance 25W E14 230-240V T25 OV 1CT/10x10F	172 lm	172 lm
924198244440	Appliance 25W E14 230-240V T25 CL OV 1CT	172 lm	172 lm
924198244442	Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	172 lm	172 lm

### Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
921096244427	Appliance 15W E14 230-240V T22 CL OV 1CT	T22
924196244402	Appliance 15W E14 230-240V T22 OV 1CT/10x10F	T22
924196244440	Appliance 15W E14 230-240V T22 CL OV 1CT	T22
924196244442	Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO	T22
924196244451	Appliance 15W E14 230-240V T22 CL OV 1BL/10	T22
924196244452	Appliance 15W E14 230-240V T22 CL OV 2BL/10	T22

Order Code	Full Product Name	Bulb Shape
924196244453	Appliance 15W E14 230-240V T22 CL OV 1BS/10	T22
921098244433	Appliance 25W E14 230-240V T25 CL OV 1CT	T25
924198244403	Appliance 25W E14 230-240V T25 OV 1CT/10x10F	T25
924198244440	Appliance 25W E14 230-240V T25 CL OV 1CT	T25
924198244442	Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	T25

## Appliance Oven Tubular

