



CoreLine Trunking – the clear choice for LED

CoreLine Trunking

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- High efficiency enables energy savings of more than 50% compared to fluorescent-based luminaires; attractive investment level and fast payback
- Good quality of light with high output to meet the requirements of demanding applications
- Easy to order and install, thus requiring less time and reducing packaging waste and complexity

Features

- Philips Fortimo LED Line 1R for high efficiency and reliability
- Advanced optics enable precise and energy-saving beam shapes
- Simplicity: only two 12 NC codes needed to make a light line
- Requires much less packaging than fluorescent, reducing total installation time

Application

- Supermarkets
- Warehouses
- Production facilities

Specifications

CoreLine Trunking

Type	LL120X (3.4 m version)
	LL120X (3.4 m standalone version: ready-to-install (KIT) with ceiling-mounting bracket (SMB))
	LL121X (1.7 m version)
	LL121X (1.7 m standalone version: ready-to-install (KIT) with ceiling-mounting bracket (SMB))
	LL122X (3.4 m half blind version)
	LL123X (3C track version)
Light source	Philips Fortimo LED Line 1R
Power	LL120X: 69 or 124 W
	LL121X: 34.5 or 62 W
Beam angle	2 x 20, 2 x 25, 2 x 30, 2 x 45, 2 x 50, 2 x 80, 1 x 30°
Luminous flux	LL120X: 9000 or 16000 lm for 4000 and 6500 K, 15200 lm for 3000 K
	LL121X: 4500 or 8000 lm for 4000 and 6500 K, 7600 lm for 3000 K
Correlated Color Temperature	3000, 4000 and 6500 K
Color Rendering Index	>80
Lumen maintenance at median useful life*	L80
50000 h	
Control gear failure rate at median useful life	5%
50000 h	
Performance Ambient Temperature Tq	+25 °C

Operating temperature range	-20 to +35 °C
Driver	Built-in (Philips Xitanium)
Mains voltage	230 or 240 V / 50-60 Hz
Dimming	DALI dimmer
Controls system input	0-16 V
Material	Housing: steel
	Lenses: PMMA or polycarbonate (for emergency lighting versions)
Color	White
Optic	Narrow, medium, wide beam, asymmetric, double asymmetric and opal optic
Optical cover	PMMA or polycarbonate
Connection	Integral male / female connectors
Maintenance	No internal cleaning required
Installation	Suspended with brackets and wire (standard)
	Surface mounted with caddy clip or bracket (additional accessories needed)
	Through-wiring standard
Accessories	Blind covers, chain brackets, profile brackets, mounting brackets for suspension wire and ceiling mounting brackets, suspension wire, electrical connectors (LL120Z)
Remarks	Emergency lighting versions battery based (3 hours, EL3) or centrally driven emergency

Versions



CoreLine trunking LL120X/LL121X luminaire, single lumen version, opal




CoreLine trunking LL122X luminaire, half blind cover and half double lumen version




CoreLine Trunking


Dimensional drawing



Product	A
LL121X LED45S/840 1x PSD DA20 7 WH	1725 mm
LL120X LED90S/840 2x PSD NB 7 VLC WH	3450 mm
LL121X 7 WH BC	
LL120X LED90S/840 2x PSU VWB 5 WH	3450 mm
LL120X LED90S/840 2x PSD DA20 7 VLC WH	3450 mm




Product	A
LL121X LED45S/840 1x PSD DA20 7 WH	1739 mm
LL120X LED90S/840 2x PSD NB 7 VLC WH	3464 mm
LL121X 7 WH BC	
LL120X LED90S/840 2x PSU VWB 5 WH	3464 mm
LL120X LED90S/840 2x PSD DA20 7 VLC WH	3464 mm



Product	A
LL121X LED45S/840 1x PSD DA20 7 WH	1999 mm
LL120X LED90S/840 2x PSD NB 7 VLC WH	3724 mm
LL121X 7 WH BC	
LL120X LED90S/840 2x PSU VWB 5 WH	3724 mm
LL120X LED90S/840 2x PSD DA20 7 VLC WH	3724 mm

Product details

IPAC1 LL120Zi 0002



IPAC1 LL120Zi 0009



CoreLine Trunking

Product details

IPAC1 LL120Zi 0025



IPAC1 LL120Zi 0007



IPAC1 LL120Zi 0003



IPAC1 LL120Zi 0013



IPAC1 LL120Zi 0015



IPAC1 LL120Zi 0023



IPAC1 LL120Zi 0017



IPAC1 LL120Zi 0012



Product details



IPPR1 LL120Xi 0002



CoreLine trunking connection



Blind cover, 5 pieces



CoreLine trunking with blind cover



9-pole connector



IPPR1 LL120Xi 0005



IPPR1 LL120Xi 0009



IPPR1 LL120Xi 0010

CoreLine Trunking

Product details



Close-up view single lumen version



Front view single lumen version



IPPR1 LL120Xi 0011

Accessories



Mounting bracket for suspension wire, 2 pieces

Ordercode 910925255035



Mounting bracket for suspension wire, 2 end pieces and connection unit 7-pole

Ordercode 910925255036



Ceiling mounting bracket

Ordercode 910925255037, 910925255170



Suspension wire Ø 2 mm, length 1.25 m

Ordercode 910925255038

Accessories




Suspension wire Ø 2 mm, length 3 m

Ordercode 910925255039



Suspension wire Ø 2 mm, length 5 m

Ordercode 910925255040




Electrical connector 7-pole male and female, 5 sets

Ordercode 910925255041



Chain bracket, 5 pieces

Ordercode 910925255042



End pieces, 6 pieces

Ordercode 910925255043



Profile bracket, 5 pieces

Ordercode 910925255044



LineSense lighting control box

Ordercode 910925255141



Ceiling mounting bracket, 2 end pieces and connection unit 7-pole

Ordercode 910925255143

Accessories



Mounting bracket for suspension wire, 2 end pieces and connection unit 9-pole

Ordercode 910925255169



CoreLine trunking LL120X/LL121X luminaire, single lumen version

Ordercode 910925682907, 910925682908, 910925682914, 910925682915, 910925682920, 910925682921, 910925682926, 910925682927, 910925682933, 910925682946, 910925682947, 910925682955, 910925682968, 910925683021, 910925683023, 910925683072, 910925772904, 910925802903, 910925863110, 910925863324, 910925863325, 910925863326, 910925863327, 910925863331, 910925863332, 910925863333, 910925863334, 910925863335, 910925863336, 910925863338



Ordercode 910925683073, 910925863969, 910925864022



CoreLine Trunking

Ordercode 910925863234, 910925863235, 910925863236, 910925863237

Application Conditions	
Suitable for random switching	No
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Initial Performance (IEC Compliant)	
Init. Color Rendering Index	≥80

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	-20 to +35 °C	-
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	-20 to +35 °C	-
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	-20 to +35 °C	Not applicable
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	-20 to +35 °C	-
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	-20 to +35 °C	-
910925682927	LL120X LED90S/840 2x PSU DA20 5 WH	-20 to +35 °C	-
910925682933	LL120X LED90S/840 2x PSD NB 7 VLC WH	-20 to +35 °C	1%
910925682946	LL121X LED45S/840 1x PSD DA20 7 WH	-20 to +35 °C	1%
910925682947	LL120X LED90S/840 2x PSD DA20 7 VLC WH	-20 to +35 °C	1%
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	-20 to +35 °C	-
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	-20 to +35 °C	-
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	-20 to +35 °C	1%
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	-20 to +35 °C	1%
910925772904	LL120X LED90S/840 2x PSD WB 7 VLC WH	-20 to +35 °C	1%
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	-20 to +35 °C	1%
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	-20 to +35 °C	1%
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	-20 to +35 °C	-
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	-20 to +35 °C	-
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	-20 to +35 °C	-
910925863327	LL120X LED90S/840 1x PSU A 5 WH	-20 to +35 °C	-
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	-20 to +35 °C	-
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	-20 to +35 °C	-
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	-20 to +35 °C	-
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	-20 to +35 °C	-
910925863335	LL120X LED90S/840 1x PSU A 7 WH	-20 to +35 °C	-
910925863336	LL120X LED90S/840 1x PSU VWB 7 WH	-20 to +35 °C	-
910925863338	LL120X LED90S/865 1x PSU WB 7 WH	-20 to +35 °C	-
910925863330	LL120X LED84S/840 1x PSU O 7 WH	-20 to +35 °C	-
910925863340	LL120X LED84S/865 1x PSU O 5 WH	-20 to +35 °C	-
910925863968	LL120X LED150S/840 2x PSD O 7 VLC WH	-20 to +35 °C	1%
910925863979	LL120X LED150S/840 2x PSU O 5 WH	-20 to +35 °C	Not applicable
910925863981	LL121X LED75S/840 1x PSD O 7 WH	-20 to +35 °C	1%
910925863957	LL121X LED80S/840 PSU WB SMB WH KIT	-20 to +35 °C	Not applicable
910925863958	LL121X LED80S/840 PSU NB SMB WH KIT	-20 to +35 °C	Not applicable
910925863959	LL121X LED80S/840 PSU WB TW3 SMB WH KIT	-20 to +35 °C	Not applicable
910925863960	LL120X LED160S/840 PSU WB SMB WH KIT	-20 to +35 °C	Not applicable
910925863961	LL120X LED160S/840 PSU NB SMB WH KIT	-20 to +35 °C	Not applicable
910925863962	LL121X LED80S/840 PSU NB TW3 SMB WH KIT	-20 to +35 °C	Not applicable
910925863963	LL120X LED160S/840 PSU WB TW3 SMB WH KIT	-20 to +35 °C	Not applicable
910925863964	LL120X LED160S/840 PSU NB TW3 SMB WH KIT	-20 to +35 °C	Not applicable
910925863965	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W	-20 to +35 °C	1%
910925863966	LL120X LED160S/840 2x PSD WB 7 VLC WH	-20 to +35 °C	1%
910925863967	LL120X LED160S/840 2x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925863970	LL120X LED160S/840 2x PSU MB 5 WH	-20 to +35 °C	Not applicable
910925863971	LL121X LED80S/840 1x PSD WB 7 WH	-20 to +35 °C	1%
910925863972	LL120X LED160S/840 2x PSU DA20 5 WH	-20 to +35 °C	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dim level
910925863973	LL121X LED80S/840 1x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925863974	LL120X LED160S/840 1x PSD WB 7 WH	-20 to +35 °C	1%
910925863975	LL120X LED160S/840 2x PSU NB 5 WH	-20 to +35 °C	Not applicable
910925863976	LL120X LED160S/840 1x PSD WB 7X2.5 WH	-20 to +35 °C	1%
910925863977	LL120X LED160S/840 2x PSD MB 7 VLC WH	-20 to +35 °C	1%
910925863978	LL120X LED160S/840 2x PSD WB 9 VLC WH	-20 to +35 °C	1%
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	-20 to +35 °C	Not applicable
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	-20 to +35 °C	1%
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	-20 to +35 °C	Not applicable
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	-20 to +35 °C	1%
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	-20 to +35 °C	1%
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	-20 to +35 °C	Not applicable
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	-20 to +35 °C	1%
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	-20 to +35 °C	1%
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	-20 to +35 °C	Not applicable
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	-20 to +35 °C	1%
910925863993	LL121X LED80S/840 1x PSU DA20 5 WH	-20 to +35 °C	Not applicable
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	-20 to +35 °C	1%
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	-20 to +35 °C	Not applicable
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	-20 to +35 °C	Not applicable
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	-20 to +35 °C	1%
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	-20 to +35 °C	1%
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	-20 to +35 °C	1%
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	-20 to +35 °C	Not applicable
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	-20 to +35 °C	Not applicable
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	-20 to +35 °C	1%
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	-20 to +35 °C	1%
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	-20 to +35 °C	Not applicable
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	-20 to +35 °C	1%
910925864009	LL120X LED160S/840 2x PSU A 5 WH	-20 to +35 °C	Not applicable
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	-20 to +35 °C	Not applicable
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	-20 to +35 °C	Not applicable
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	-20 to +35 °C	1%
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	-20 to +35 °C	1%
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	-20 to +35 °C	1%
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	-20 to +35 °C	1%
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	-20 to +35 °C	1%
910925864019	LL121X LED80S/840 1x PSU A 5 WH	-20 to +35 °C	Not applicable
910925864020	LL120X LED152S/830 2x PSU A 5 WH	-20 to +35 °C	Not applicable
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	-20 to +35 °C	1%
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	-20 to +35 °C	1%
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	-20 to +35 °C	1%
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	-20 to +35 °C	Not applicable
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	-20 to +35 °C	1%
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	-20 to +35 °C	Not applicable
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	-20 to +35 °C	1%
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	-20 to +35 °C	Not applicable
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	-20 to +35 °C	1%

Order Code	Full Product Name	Ambient temperature range	Maximum dim level
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	-20 to +35 °C	Not applicable
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	-20 to +35 °C	Not applicable
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	-20 to +35 °C	Not applicable
910925864035	LL121X LED80S/840 1x PSD A 7 WH	-20 to +35 °C	1%
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	-20 to +35 °C	Not applicable
910925864037	LL121X LED80S/840 1x PSU WB 7 WH	-20 to +35 °C	Not applicable
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	-20 to +35 °C	1%
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	-20 to +35 °C	1%
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	-20 to +35 °C	1%
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	-20 to +35 °C	Not applicable
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	-20 to +35 °C	Not applicable
910925864043	LL121X LED76S/830 1x PSU A 5 WH	-20 to +35 °C	Not applicable
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	-20 to +35 °C	Not applicable
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	-20 to +35 °C	1%
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	-20 to +35 °C	Not applicable
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	-20 to +35 °C	Not applicable
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	-20 to +35 °C	Not applicable
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	-20 to +35 °C	Not applicable
910925864053	LL121X LED76S/830 1x PSD A 7 WH	-20 to +35 °C	1%
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	-20 to +35 °C	Not applicable
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	-20 to +35 °C	Not applicable
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	-20 to +35 °C	1%
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	-20 to +35 °C	Not applicable
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	-20 to +35 °C	Not applicable
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	-20 to +35 °C	Not applicable
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	-20 to +35 °C	Not applicable
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	-20 to +35 °C	Not applicable
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	-20 to +35 °C	1%
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 VLC	-20 to +35 °C	1%
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	-20 to +35 °C	1%
910925864066	LL121X LED80S/840 1x PSD VWB 7X2.5 WH	-20 to +35 °C	1%
910925864067	LL122X LED80S/840 1x PSD NB 7X2.5 WH	-20 to +35 °C	1%
910925864068	LL121X LED80S/840 1x PSU MB 7 EL3 WH	-20 to +35 °C	Not applicable
910925864069	LL120X LED160S/865 1x PSD MB 7 WH	-20 to +35 °C	1%
910925864070	LL120X LED160S/865 2x PSU MB 5 WH	-20 to +35 °C	Not applicable
910925864071	LL121X LED80S/840 1x PSD NB 9 EL3 WH	-20 to +35 °C	1%
910925864629	LL121X LED76S/830 PSU WB TW3 SMB WH KIT	-20 to +35 °C	Not applicable
910925864630	LL121X LED76S/830 PSU WB EL3 TW3 WH KIT	-20 to +35 °C	Not applicable
910925864646	LL121X LED80S/840 PSD WB WH KIT	-20 to +30 °C	1%
910925864647	LL121X LED80S/840 PSD NB WH KIT	-20 to +35 °C	1%
910925863969	LL120X LED150S/840 1x PSD O 7 WH	-20 to +35 °C	1%
910925864022	LL120X LED150S/865 2x PSU O 5 WH	-20 to +35 °C	Not applicable
910925864540	LL120X LED150S/840 1x PSD PCO 7 WH	+20 to +35 °C	1%
910925864541	LL120X LED150S/840 2x PSD PCO 7 VLC WH	+20 to +35 °C	1%
910925864542	LL121X LED75S/840 1x PSD PCO 7 WH	+20 to +35 °C	1%
910925864543	LL120X LED150S/840 2x PSU PCO 5 WH	+20 to +35 °C	Not applicable
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	+20 to +35 °C	Not applicable
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	+20 to +35 °C	1%
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	+20 to +35 °C	Not applicable

Controls and Dimming

CoreLine Trunking

Order Code	Full Product Name	Dimmable
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	No
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	No
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	No
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	No
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	No
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	No
910925682927	LL120X LED90S/840 2x PSU DA20 5 WH	No
910925682933	LL120X LED90S/840 2x PSD NB 7 VLC WH	Yes
910925682946	LL121X LED45S/840 1x PSD DA20 7 WH	Yes
910925682947	LL120X LED90S/840 2x PSD DA20 7 VLC WH	Yes
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	No
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	No
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	Yes
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	Yes
910925772904	LL120X LED90S/840 2x PSD WB 7 VLC WH	Yes
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	Yes
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	Yes
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	No
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	No
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	No
910925863327	LL120X LED90S/840 1x PSU A 5 WH	No
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	No
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	No
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	No
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	No
910925863335	LL120X LED90S/840 1x PSU A 7 WH	No
910925863336	LL120X LED90S/840 1x PSU VWB 7 WH	No
910925863338	LL120X LED90S/865 1x PSU WB 7 WH	No
910925863330	LL120X LED84S/840 1x PSU O 7 WH	No
910925863340	LL120X LED84S/865 1x PSU O 5 WH	No
910925863968	LL120X LED150S/840 2x PSD O 7 VLC WH	Yes
910925863979	LL120X LED150S/840 2x PSU O 5 WH	No
910925863981	LL121X LED75S/840 1x PSD O 7 WH	Yes
910925863957	LL121X LED80S/840 PSU WB SMB WH KIT	No
910925863958	LL121X LED80S/840 PSU NB SMB WH KIT	No
910925863959	LL121X LED80S/840 PSU WB TW3 SMB WH KIT	No
910925863960	LL120X LED160S/840 PSU WB SMB WH KIT	No
910925863961	LL120X LED160S/840 PSU NB SMB WH KIT	No
910925863962	LL121X LED80S/840 PSU NB TW3 SMB WH KIT	No
910925863963	LL120X LED160S/840 PSU WB TW3 SMB WH KIT	No
910925863964	LL120X LED160S/840 PSU NB TW3 SMB WH KIT	No
910925863965	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W	Yes
910925863966	LL120X LED160S/840 2x PSD WB 7 VLC WH	Yes
910925863967	LL120X LED160S/840 2x PSU WB 5 WH	No
910925863970	LL120X LED160S/840 2x PSU MB 5 WH	No
910925863971	LL121X LED80S/840 1x PSD WB 7 WH	Yes
910925863972	LL120X LED160S/840 2x PSU DA20 5 WH	No
910925863973	LL121X LED80S/840 1x PSU WB 5 WH	No
910925863974	LL120X LED160S/840 1x PSD WB 7 WH	Yes
910925863975	LL120X LED160S/840 2x PSU NB 5 WH	No
910925863976	LL120X LED160S/840 1x PSD WB 7X2.5 WH	Yes
910925863977	LL120X LED160S/840 2x PSD MB 7 VLC WH	Yes

Order Code	Full Product Name	Dimmable
910925863978	LL120X LED160S/840 2x PSD WB 9 VLC WH	Yes
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	No
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	No
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	No
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	Yes
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	No
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	Yes
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	Yes
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	No
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	Yes
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	Yes
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	No
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	Yes
910925863993	LL121X LED80S/840 1x PSU DA20 5 WH	No
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	Yes
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	No
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	No
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	Yes
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	Yes
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	Yes
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	No
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	No
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	Yes
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	Yes
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	No
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	Yes
910925864009	LL120X LED160S/840 2x PSU A 5 WH	No
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	No
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	No
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	No
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	Yes
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	Yes
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	Yes
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	Yes
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	Yes
910925864019	LL121X LED80S/840 1x PSU A 5 WH	No
910925864020	LL120X LED152S/830 2x PSU A 5 WH	No
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	Yes
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	Yes
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	Yes
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	No
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	Yes
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	No
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	Yes
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	No
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	Yes
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	No
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	No
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	No
910925864035	LL121X LED80S/840 1x PSD A 7 WH	Yes
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	No
910925864037	LL121X LED80S/840 1x PSU WB 7 WH	No

CoreLine Trunking

Order Code	Full Product Name	Dimmable
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	Yes
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	Yes
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	Yes
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	No
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	No
910925864043	LL121X LED76S/830 1x PSU A 5 WH	No
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	No
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	Yes
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	No
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	No
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	No
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	No
910925864053	LL121X LED76S/830 1x PSD A 7 WH	Yes
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	No
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	No
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	Yes
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	No
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	No
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	No
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	No
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	No
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	Yes

Operating and Electrical

Order Code	Full Product Name	Circuit
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	-
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	-
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	-
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	-
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	-
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	-
910925682927	LL120X LED90S/840 2x PSU DA20 5 WH	-
910925682933	LL120X LED90S/840 2x PSD NB 7 VLC WH	-
910925682946	LL121X LED45S/840 1x PSD DA20 7 WH	-
910925682947	LL120X LED90S/840 2x PSD DA20 7 VLC WH	-
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	-
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	-
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	-
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	-
910925772904	LL120X LED90S/840 2x PSD WB 7 VLC WH	-
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	-
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	-
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	-
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	-
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	-
910925863327	LL120X LED90S/840 1x PSU A 5 WH	-
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	-
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	-
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	-
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	-
910925863335	LL120X LED90S/840 1x PSU A 7 WH	-

Order Code	Full Product Name	Dimmable
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 VLC	Yes
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	Yes
910925864066	LL121X LED80S/840 1x PSD VWB 7X2.5 WH	Yes
910925864067	LL122X LED80S/840 1x PSD NB 7X2.5 WH	Yes
910925864068	LL121X LED80S/840 1x PSU MB 7 EL3 WH	No
910925864069	LL120X LED160S/865 1x PSD MB 7 WH	Yes
910925864070	LL120X LED160S/865 2x PSU MB 5 WH	No
910925864071	LL121X LED80S/840 1x PSD NB 9 EL3 WH	Yes
910925864629	LL121X LED76S/830 PSU WB TW3 SMB WH KIT	No
910925864630	LL121X LED76S/830 PSU WB EL3 TW3 WH KIT	No
910925864646	LL121X LED80S/840 PSD WB WH KIT	Yes
910925864647	LL121X LED80S/840 PSD NB WH KIT	Yes
910925863969	LL120X LED150S/840 1x PSD O 7 WH	Yes
910925864022	LL120X LED150S/865 2x PSU O 5 WH	No
910925864540	LL120X LED150S/840 1x PSD PCO 7 WH	Yes
910925864541	LL120X LED150S/840 2x PSD PCO 7 VLC WH	Yes
910925864542	LL121X LED75S/840 1x PSD PCO 7 WH	Yes
910925864543	LL120X LED150S/840 2x PSU PCO 5 WH	No
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	No
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	Yes
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	No

CoreLine Trunking

Order Code	Full Product Name	Circuit
910925863978	LL120X LED160S/840 2x PSD WB 9 VLC WH	-
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	-
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	-
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	-
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	-
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	-
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	-
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	-
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	-
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	-
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	-
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	-
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	-
910925863993	LL121X LED80S/840 1x PSU DA20 5 WH	-
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	-
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	-
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	-
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	-
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	-
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	-
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	-
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	-
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	-
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	-
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	-
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	-
910925864009	LL120X LED160S/840 2x PSU A 5 WH	-
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	-
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	-
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	-
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	-
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	-
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	-
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	-
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	-
910925864019	LL121X LED80S/840 1x PSU A 5 WH	-
910925864020	LL120X LED152S/830 2x PSU A 5 WH	-
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	-
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	-
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	-
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	-
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	-
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	-
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	-
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	-
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	-
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	-
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	-

Order Code	Full Product Name	Circuit
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	-
910925864035	LL121X LED80S/840 1x PSD A 7 WH	-
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	-
910925864037	LL121X LED80S/840 1x PSU WB 7 WH	-
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	-
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	-
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	-
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	-
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	-
910925864043	LL121X LED76S/830 1x PSU A 5 WH	-
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	-
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	-
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	-
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	-
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	-
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	-
910925864053	LL121X LED76S/830 1x PSD A 7 WH	-
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	-
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	-
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	-
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	-
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	-
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	-
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	-
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	-
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	-
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 VLC	-
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	-
910925864066	LL121X LED80S/840 1x PSD VWB 7X2.5 WH	-
910925864067	LL122X LED80S/840 1x PSD NB 7X2.5 WH	-
910925864068	LL121X LED80S/840 1x PSU MB 7 EL3 WH	-
910925864069	LL120X LED160S/865 1x PSD MB 7 WH	-
910925864070	LL120X LED160S/865 2x PSU MB 5 WH	-
910925864071	LL121X LED80S/840 1x PSD NB 9 EL3 WH	-
910925864629	LL121X LED76S/830 PSU WB TW3 SMB WH KIT	-
910925864630	LL121X LED76S/830 PSU WB EL3 TW3 WH KIT	-
910925864646	LL121X LED80S/840 PSD WB WH KIT	-
910925864647	LL121X LED80S/840 PSD NB WH KIT	-
910925863969	LL120X LED150S/840 1x PSD O 7 WH	-
910925864022	LL120X LED150S/865 2x PSU O 5 WH	-
910925864540	LL120X LED150S/840 1x PSD PCO 7 WH	-
910925864541	LL120X LED150S/840 2x PSD PCO 7 VLC WH	-
910925864542	LL121X LED75S/840 1x PSD PCO 7 WH	-
910925864543	LL120X LED150S/840 2x PSU PCO 5 WH	-
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	-
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	-
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	-

General Information (1/2)

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/ lens Emergency		
			type	lighting	Glow-wire test
910925682908	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSU NB 5	suspension			5 s
	WH	wire			
910925682914	LL121X	Mounting	-	-	Temperature
	LED45S/840	bracket for			650 °C, duration
	1x PSU MB 5	suspension			5 s
	WH	wire			
910925682915	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSU MB 5	suspension			5 s
	WH	wire			
910925682920	LL121X	Mounting	-	-	Temperature
	LED45S/840	bracket for			650 °C, duration
	1x PSU WB 5	suspension			5 s
	WH	wire			
910925682921	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSU WB 5	suspension			5 s
	WH	wire			
910925682926	LL121X	Mounting	-	-	Temperature
	LED45S/840	bracket for			650 °C, duration
	1x PSU DA20	suspension			5 s
	5 WH	wire			
910925682927	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSU DA20	suspension			5 s
	5 WH	wire			
910925682933	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSD NB 7	suspension			5 s
	VLC WH	wire			
910925682946	LL121X	Mounting	-	-	Temperature
	LED45S/840	bracket for			650 °C, duration
	1x PSD DA20 7	suspension			5 s
	WH	wire			
910925682947	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSD DA20	suspension			5 s
	7 VLC WH	wire			
910925682955	LL121X	Mounting	-	-	Temperature
	LED45S/840	bracket for			650 °C, duration
	1x PSU NB 5	suspension			5 s
	WH	wire			
910925682968	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSU VWB 5	suspension			5 s
	WH	wire			

Order Code	Full Product Name	Accessories included	Optical cover/ lens Emergency		
			type	lighting	Glow-wire test
910925683021	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSD WB 9	suspension			5 s
	VLC WH	wire			
910925683023	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSD VWB 9	suspension			5 s
	VLC WH	wire			
910925772904	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	2x PSD WB 7	suspension			5 s
	VLC WH	wire			
910925802903	LL121X	Mounting	-	-	Temperature
	LED45S/840	bracket for			650 °C, duration
	1x PSD WB 7	suspension			5 s
	WH	wire			
910925863110	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSD WB 9	suspension			5 s
	WH	wire			
910925863324	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU NB 5	suspension			5 s
	WH	wire			
910925863325	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU MB 5	suspension			5 s
	WH	wire			
910925863326	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU DA20	suspension			5 s
	5 WH	wire			
910925863327	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU A 5	suspension			5 s
	WH	wire			
910925863331	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU DA20 7	suspension			5 s
	WH	wire			
910925863332	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU MB 7	suspension			5 s
	WH	wire			
910925863333	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU NB 7	suspension			5 s
	WH	wire			

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/ lens Emergency		
			type	lighting	Glow-wire test
910925863334	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU WB 7	suspension			5 s
	WH	wire			
910925863335	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU A 7 WH	suspension			5 s
		wire			
910925863336	LL120X	Mounting	-	-	Temperature
	LED90S/840	bracket for			650 °C, duration
	1x PSU VWB 7	suspension			5 s
	WH	wire			
910925863338	LL120X	Mounting	-	-	Temperature
	LED90S/865	bracket for			650 °C, duration
	1x PSU WB 7	suspension			5 s
	WH	wire			
910925863330	LL120X	Mounting	Opal	-	Temperature
	LED84S/840	bracket for			850 °C, duration
	1x PSU O 7	suspension			5 s
	WH	wire			
910925863340	LL120X	Mounting	Opal	-	Temperature
	LED84S/865	bracket for			850 °C, duration
	1x PSU O 5	suspension			5 s
	WH	wire			
910925863968	LL120X	Mounting	Opal	-	Temperature
	LED150S/840	bracket for			650 °C, duration
	2x PSD O 7	suspension			5 s
	VLC WH	wire			
910925863979	LL120X	Mounting	Opal	-	Temperature
	LED150S/840	bracket for			650 °C, duration
	2x PSU O 5	suspension			5 s
	WH	wire			
910925863981	LL121X	Mounting	Opal	-	Temperature
	LED75S/840	bracket for			650 °C, duration
	1x PSD O 7	suspension			5 s
	WH	wire			
910925863957	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	PSU WB SMB	suspension			5 s
	WH KIT	wire			
910925863958	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	PSU NB SMB	suspension			5 s
	WH KIT	wire			
910925863959	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	PSU WB TW3	suspension			5 s
	SMB WH KIT	wire			

Order Code	Full Product Name	Accessories included	Optical cover/ lens Emergency		
			type	lighting	Glow-wire test
910925863960	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	PSU WB SMB	suspension			5 s
	WH KIT	wire			
910925863961	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	PSU NB SMB	suspension			5 s
	WH KIT	wire			
910925863962	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	PSU NB TW3	suspension			5 s
	SMB WH KIT	wire			
910925863963	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	PSU WB TW3	suspension			5 s
	SMB WH KIT	wire			
910925863964	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	PSU NB TW3	suspension			5 s
	SMB WH KIT	wire			
910925863965	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD WB	suspension			5 s
	7X2.5 VLC W	wire			
910925863966	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD WB 7	suspension			5 s
	VLC WH	wire			
910925863967	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU WB 5	suspension			5 s
	WH	wire			
910925863970	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU MB 5	suspension			5 s
	WH	wire			
910925863971	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD WB 7	suspension			5 s
	WH	wire			
910925863972	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU DA20	suspension			5 s
	5 WH	wire			
910925863973	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU WB 5	suspension			5 s
	WH	wire			

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/ lens Emergency		
			type	lighting	Glow-wire test
910925863974	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	1x PSD WB 7	suspension			5 s
	WH	wire			
910925863975	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU NB 5	suspension			5 s
	WH	wire			
910925863976	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	1x PSD WB	suspension			5 s
	7X2.5 WH	wire			
910925863977	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD MB 7	suspension			5 s
	VLC WH	wire			
910925863978	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD WB 9	suspension			5 s
	VLC WH	wire			
910925863980	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU WB 5	suspension			5 s
	WH	wire			
910925863982	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU MB 5	suspension			5 s
	WH	wire			
910925863983	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSU WB 5	suspension			5 s
	WH	wire			
910925863984	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD VWB 7	suspension			5 s
	VLC WH	wire			
910925863985	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSU VWB 5	suspension			5 s
	WH	wire			
910925863986	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	1x PSD NB 7	suspension			5 s
	WH	wire			
910925863987	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	1x PSD MB 7	suspension			5 s
	WH	wire			

Order Code	Full Product Name	Accessories included	Optical cover/ lens Emergency		
			type	lighting	Glow-wire test
910925863988	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSU DA20	suspension			5 s
	5 WH	wire			
910925863989	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD NB 9	suspension			5 s
	VLC WH	wire			
910925863990	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD WB	suspension			5 s
	7X2.5 WH	wire			
910925863991	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU WB 7	suspension			5 s
	WH	wire			
910925863992	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD NB 7	suspension			5 s
	VLC WH	wire			
910925863993	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU DA20	suspension			5 s
	5 WH	wire			
910925863994	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSD WB 7	suspension			5 s
	VLC WH	wire			
910925863995	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSU MB 5	suspension			5 s
	WH	wire			
910925863996	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU VWB 5	suspension			5 s
	WH	wire			
910925863997	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSD WB 7	suspension			5 s
	WH	wire			
910925863998	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD A	suspension			5 s
	7X2.5 VLC WH	wire			
910925863999	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD NB 7	suspension			5 s
	WH	wire			

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/ lens type		
			Emergency lighting	Emergency lighting 3 hours duration	Glow-wire test
910925864002	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU VWB 5	suspension			5 s
	WH	wire			
910925864003	LL121X	Mounting	-	Emergency lighting 3 hours duration	Temperature
	LED80S/840	bracket for			850 °C, duration
	1x PSU WB 7	suspension			5 s
	EL3 WH	wire			
910925864004	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD MB 7	suspension			5 s
	WH	wire			
910925864005	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD WB 9	suspension			5 s
	WH	wire			
910925864007	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU NB 5	suspension			5 s
	WH	wire			
910925864008	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD NB 9	suspension			5 s
	WH	wire			
910925864009	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU A 5	suspension			5 s
	WH	wire			
910925864010	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU WB 5	suspension			5 s
	WH	wire			
910925864011	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU VWB 5	suspension			5 s
	WH	wire			
910925864012	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU MB 5	suspension			5 s
	WH	wire			
910925864013	LL121X	Mounting	-	Emergency lighting 3 hours duration	Temperature
	LED80S/840	bracket for			850 °C, duration
	1x PSD WB 9	suspension			5 s
	EL3 WH	wire			
910925864014	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD MB 9	suspension			5 s
	VLC WH	wire			

Order Code	Full Product Name	Accessories included	Optical cover/ lens type		
			Emergency lighting	Emergency lighting 3 hours duration	Glow-wire test
910925864016	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD DA20	suspension			5 s
	7 VLC WH	wire			
910925864017	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD DA20 7	suspension			5 s
	WH	wire			
910925864018	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD A 7	suspension			5 s
	VLC WH	wire			
910925864019	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU A 5	suspension			5 s
	WH	wire			
910925864020	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSU A 5	suspension			5 s
	WH	wire			
910925864021	LL120X	Mounting	-	-	Temperature
	LED160S/865	bracket for			650 °C, duration
	2x PSD VWB 7	suspension			5 s
	VLC WH	wire			
910925864023	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD MB 9	suspension			5 s
	WH	wire			
910925864024	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD VWB 7	suspension			5 s
	WH	wire			
910925864025	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU MB 7	suspension			5 s
	WH	wire			
910925864026	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD VWB 7	suspension			5 s
	WH	wire			
910925864028	LL120X	Mounting	-	-	Temperature
	LED160S/865	bracket for			650 °C, duration
	2x PSU WB 5	suspension			5 s
	WH	wire			
910925864029	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD WB 9	suspension			5 s
	WH	wire			

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/		Glow-wire test
			lens type	Emergency lighting	
910925864030	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU WB	suspension			5 s
	7X2.5 WH	wire			
910925864031	LL120X	Mounting	-	-	Temperature
	LED152S/830	bracket for			650 °C, duration
	2x PSD DA20	suspension			5 s
	7 VLC WH	wire			
910925864032	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU DA20	suspension			5 s
	5 WH	wire			
910925864033	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU NB	suspension			5 s
	7X2.5 WH	wire			
910925864034	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU VWB 5	suspension			5 s
	WH	wire			
910925864035	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD A 7	suspension			5 s
	WH	wire			
910925864036	LL122X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU VWB 7	suspension			5 s
	WH	wire			
910925864037	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU WB 7	suspension			5 s
	WH	wire			
910925864038	LL120X	Mounting	-	-	Temperature
	LED160S/865	bracket for			650 °C, duration
	2x PSD MB 7	suspension			5 s
	VLC WH	wire			
910925864039	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSD WB 9	suspension			5 s
	WH	wire			
910925864040	LL121X	Mounting	-	-	Temperature
	LED80S/865	bracket for			650 °C, duration
	1x PSD WB 7	suspension			5 s
	WH	wire			
910925864041	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU MB 7	suspension			5 s
	WH	wire			

Order Code	Full Product Name	Accessories included	Optical cover/		Glow-wire test
			lens type	Emergency lighting	
910925864042	LL121X	Mounting	-	Emergency	Temperature
	LED76S/830	bracket for		lighting 3	850 °C, duration
	1x PSU VWB 7	suspension		hours	5 s
	EL3 WH	wire		duration	
910925864043	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU A 5	suspension			5 s
	WH	wire			
910925864045	LL121X	Mounting	-	Emergency	Temperature
	LED80S/840	bracket for		lighting 3	850 °C, duration
	1x PSU DA20 7	suspension		hours	5 s
	EL3 WH	wire		duration	
910925864046	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD A	suspension			5 s
	7X2.5 WH	wire			
910925864047	LL121X	Mounting	-	Emergency	Temperature
	LED80S/840	bracket for		lighting 3	850 °C, duration
	1x PSU NB 7	suspension		hours	5 s
	EL3 WH	wire		duration	
910925864048	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU NB 7	suspension			5 s
	WH	wire			
910925864049	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSU VWB 7	suspension			5 s
	WH	wire			
910925864051	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU NB 7	suspension			5 s
	WH	wire			
910925864053	LL121X	Mounting	-	-	Temperature
	LED76S/830	bracket for			650 °C, duration
	1x PSD A 7	suspension			5 s
	WH	wire			
910925864055	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU VWB 7	suspension			5 s
	WH	wire			
910925864056	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU VWB 7	suspension			5 s
	WH	wire			
910925864057	LL121X	Mounting	-	-	Temperature
	LED80S/865	bracket for			650 °C, duration
	1x PSD MB 9	suspension			5 s
	WH	wire			

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/		Glow-wire test
			lens type	Emergency lighting	
910925864058	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU WB	suspension			5 s
	5X2.5 WH	wire			
910925864059	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSU VWB	suspension			5 s
	5X2.5 WH	wire			
910925864060	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU VWB	suspension			5 s
	5X2.5 WH	wire			
910925864061	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU VWB	suspension			5 s
	5X2.5 WH	wire			
910925864062	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSU NB	suspension			5 s
	5X2.5 WH	wire			
910925864063	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD WB	suspension			5 s
	7X2.5 WH	wire			
910925864064	LL120X	Mounting	-	-	Temperature
	LED160S/840	bracket for			650 °C, duration
	2x PSD VWB	suspension			5 s
	7X2.5 VLC	wire			
910925864065	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD VWB	suspension			5 s
	7X2.5 WH	wire			
910925864066	LL121X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD VWB	suspension			5 s
	7X2.5 WH	wire			
910925864067	LL122X	Mounting	-	-	Temperature
	LED80S/840	bracket for			650 °C, duration
	1x PSD NB	suspension			5 s
	7X2.5 WH	wire			
910925864068	LL121X	Mounting	-	Emergency lighting	Temperature
	LED80S/840	bracket for		3 hours	850 °C, duration
	1x PSU MB 7	suspension			5 s
	EL3 WH	wire		duration	
910925864069	LL120X	Mounting	-	-	Temperature
	LED160S/865	bracket for			650 °C, duration
	1x PSD MB 7	suspension			5 s
	WH	wire			

Order Code	Full Product Name	Accessories included	Optical cover/		Glow-wire test
			lens type	Emergency lighting	
910925864070	LL120X	Mounting	-	-	Temperature
	LED160S/865	bracket for			650 °C, duration
	2x PSU MB 5	suspension			5 s
	WH	wire			
910925864071	LL121X	Mounting	-	Emergency lighting	Temperature
	LED80S/840	bracket for		3 hours	850 °C, duration
	1x PSD NB 9	suspension			5 s
	EL3 WH	wire		duration	
910925864629	LL121X	-	-	-	Temperature
	LED76S/830				650 °C, duration
	PSU WB TW3				5 s
	SMB WH KIT				
910925864630	LL121X	-	-	-	Temperature
	LED76S/830				650 °C, duration
	PSU WB EL3				5 s
	TW3 WH KIT				
910925864646	LL121X	-	-	-	Temperature
	LED80S/840				650 °C, duration
	PSD WB WH				5 s
	KIT				
910925864647	LL121X	-	-	-	Temperature
	LED80S/840				650 °C, duration
	PSD NB WH				5 s
	KIT				
910925863969	LL120X	Mounting	Opal	-	Temperature
	LED150S/840	bracket for			650 °C, duration
	1x PSD O 7	suspension			5 s
	WH	wire			
910925864022	LL120X	Mounting	Opal	-	Temperature
	LED150S/865	bracket for			650 °C, duration
	2x PSU O 5	suspension			5 s
	WH	wire			
910925864540	LL120X	-	-	-	Temperature
	LED150S/840				650 °C, duration
	1x PSD PCO 7				5 s
	WH				
910925864541	LL120X	-	-	-	Temperature
	LED150S/840				650 °C, duration
	2x PSD PCO 7				5 s
	VLC WH				
910925864542	LL121X	-	-	-	Temperature
	LED75S/840				650 °C, duration
	1x PSD PCO 7				5 s
	WH				
910925864543	LL120X	-	-	-	Temperature
	LED150S/840				650 °C, duration
	2x PSU PCO 5				5 s
	WH				

CoreLine Trunking

Order Code	Full Product Name	Accessories included	Optical cover/ lens type	Emergency lighting	Glow-wire test
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	-	-	-	Temperature 650 °C, duration 5 s
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	-	-	-	Temperature 850 °C, duration 5 s

Order Code	Full Product Name	Accessories included	Optical cover/ lens type	Emergency lighting	Glow-wire test
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	-	-	-	Temperature 850 °C, duration 5 s

General Information (2/2)

Order Code	Full Product Name	Lamp family code	Mechanical accessories	Number of gear units	Number of light sources	Optic type	Product Family Code	Internal wiring
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	LED90S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	LED45S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	LED90S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	LED45S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	LED90S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	LED45S	-	1 unit	3 pcs	Double asymmetric optic 20°	LL121X	Standard
910925682927	LL120X LED90S/840 2x PSU DA20 5 WH	LED90S	-	2 units	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925682933	LL120X LED90S/840 2x PSD NB 7 VLC WH	LED90S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925682946	LL121X LED45S/840 1x PSD DA20 7 WH	LED45S	-	1 unit	3 pcs	Double asymmetric optic 20°	LL121X	Standard
910925682947	LL120X LED90S/840 2x PSD DA20 7 VLC WH	LED90S	-	2 units	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	LED45S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	LED90S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	LED90S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	LED90S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925772904	LL120X LED90S/840 2x PSD WB 7 VLC WH	LED90S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	LED45S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	LED90S	-	1 unit	6 pcs	Wide beam	LL120X	Standard
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	LED90S	-	1 unit	6 pcs	Narrow beam	LL120X	Standard
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	LED90S	-	1 unit	6 pcs	Medium beam	LL120X	Standard
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	LED90S	-	1 unit	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925863327	LL120X LED90S/840 1x PSU A 5 WH	LED90S	-	1 unit	6 pcs	Asymmetrical mirror	LL120X	Standard
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	LED90S	-	1 unit	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	LED90S	-	1 unit	6 pcs	Medium beam	LL120X	Standard
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	LED90S	-	1 unit	6 pcs	Narrow beam	LL120X	Standard
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	LED90S	-	1 unit	6 pcs	Wide beam	LL120X	Standard
910925863335	LL120X LED90S/840 1x PSU A 7 WH	LED90S	-	1 unit	6 pcs	Asymmetrical mirror	LL120X	Standard
910925863336	LL120X LED90S/840 1x PSU VWB 7 WH	LED90S	-	1 unit	6 pcs	Very wide beam	LL120X	Standard
910925863338	LL120X LED90S/865 1x PSU WB 7 WH	LED90S	-	1 unit	6 pcs	Wide beam	LL120X	Standard

CoreLine Trunking

Order Code	Full Product Name	Lamp family code	Mechanical accessories	Number of gear units	Number of light sources	Optic type	Product Family Code	Internal wiring
910925863330	LL120X LED84S/840 1x PSU O 7 WH	LED84S	-	1 unit	6 pcs	-	LL120X	Standard
910925863340	LL120X LED84S/865 1x PSU O 5 WH	LED84S	-	1 unit	6 pcs	-	LL120X	Standard
910925863968	LL120X LED150S/840 2x PSD O 7 VLC WH	LED150S	-	2 units	6 pcs	-	LL120X	Standard
910925863979	LL120X LED150S/840 2x PSU O 5 WH	LED150S	-	2 units	6 pcs	-	LL120X	Standard
910925863981	LL121X LED75S/840 1x PSD O 7 WH	LED75S	-	1 unit	3 pcs	-	LL121X	Standard
910925863957	LL121X LED80S/840 PSU WB SMB WH KIT	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863958	LL121X LED80S/840 PSU NB SMB WH KIT	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925863959	LL121X LED80S/840 PSU WB TW3 SMB WH KIT	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863960	LL120X LED160S/840 PSU WB SMB WH KIT	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863961	LL120X LED160S/840 PSU NB SMB WH KIT	LED160S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925863962	LL121X LED80S/840 PSU NB TW3 SMB WH KIT	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925863963	LL120X LED160S/840 PSU WB TW3 SMB WH KIT	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863964	LL120X LED160S/840 PSU NB TW3 SMB WH KIT	LED160S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925863965	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863966	LL120X LED160S/840 2x PSD WB 7 VLC WH	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863967	LL120X LED160S/840 2x PSU WB 5 WH	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863970	LL120X LED160S/840 2x PSU MB 5 WH	LED160S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925863971	LL121X LED80S/840 1x PSD WB 7 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863972	LL120X LED160S/840 2x PSU DA20 5 WH	LED160S	-	2 units	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925863973	LL121X LED80S/840 1x PSU WB 5 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863974	LL120X LED160S/840 1x PSD WB 7 WH	LED160S	-	1 unit	6 pcs	Wide beam	LL120X	Standard
910925863975	LL120X LED160S/840 2x PSU NB 5 WH	LED160S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925863976	LL120X LED160S/840 1x PSD WB 7X2.5 WH	LED160S	-	1 unit	6 pcs	Wide beam	LL120X	Standard
910925863977	LL120X LED160S/840 2x PSD MB 7 VLC WH	LED160S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925863978	LL120X LED160S/840 2x PSD WB 9 VLC WH	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	LED76S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	LED80S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	LED152S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	LED160S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	LED152S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	LED160S	-	1 unit	6 pcs	Narrow beam	LL120X	Standard
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	LED160S	-	1 unit	6 pcs	Medium beam	LL120X	Standard
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	LED152S	-	2 units	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	LED160S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	LED160S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925863993	LL121X LED80S/840 1x PSU DA20 5 WH	LED80S	-	1 unit	3 pcs	Double asymmetric optic 20°	LL121X	Standard
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	LED152S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	LED152S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	LED160S	-	2 units	6 pcs	Very wide beam	LL120X	Standard

CoreLine Trunking

Order Code	Full Product Name	Lamp family code	Mechanical accessories	Number of gear units	Number of light sources	Optic type	Product Family Code	Internal wiring
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	LED76S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	LED160S	-	2 units	6 pcs	Asymmetrical mirror	LL120X	Standard
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	LED80S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864009	LL120X LED160S/840 2x PSU A 5 WH	LED160S	-	2 units	6 pcs	Asymmetrical mirror	LL120X	Standard
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL122X	Standard
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL122X	Standard
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	LED76S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	LED160S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	LED160S	-	2 units	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	LED80S	-	1 unit	3 pcs	Double asymmetric optic 20°	LL121X	Standard
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	LED160S	-	2 units	6 pcs	Asymmetrical mirror	LL120X	Standard
910925864019	LL121X LED80S/840 1x PSU A 5 WH	LED80S	-	1 unit	3 pcs	Asymmetrical mirror	LL121X	Standard
910925864020	LL120X LED152S/830 2x PSU A 5 WH	LED152S	-	2 units	6 pcs	Asymmetrical mirror	LL120X	Standard
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	LED160S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	LED80S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	LED80S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL122X	Standard
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	LED160S	-	2 units	6 pcs	Wide beam	LL120X	Standard
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL122X	Standard
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	LED152S	-	2 units	6 pcs	Double asymmetric optic 20°	LL120X	Standard
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	LED76S	-	1 unit	3 pcs	Double asymmetric optic 20°	LL121X	Standard
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	LED76S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864035	LL121X LED80S/840 1x PSD A 7 WH	LED80S	-	1 unit	3 pcs	Asymmetrical mirror	LL121X	Standard
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	LED76S	-	1 unit	3 pcs	Very wide beam	LL122X	Standard
910925864037	LL121X LED80S/840 1x PSU WB 7 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	LED160S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	LED76S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL121X	Standard
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	LED160S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	LED76S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864043	LL121X LED76S/830 1x PSU A 5 WH	LED76S	-	1 unit	3 pcs	Asymmetrical mirror	LL121X	Standard
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	LED80S	-	1 unit	3 pcs	Double asymmetric optic 20°	LL121X	Standard
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	LED80S	-	1 unit	3 pcs	Asymmetrical mirror	LL121X	Standard

CoreLine Trunking

Order Code	Full Product Name	Lamp family code	Mechanical accessories	Number of gear units	Number of light sources	Optic type	Product Family Code	Internal wiring
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	LED160S	-	2 units	6 pcs	Narrow beam	LL120X	Standard
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	LED76S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864053	LL121X LED76S/830 1x PSD A 7 WH	LED76S	-	1 unit	3 pcs	Asymmetrical mirror	LL121X	Standard
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	LED160S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	LED80S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL122X	Standard
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	LED160S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL122X	Standard
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL122X	Standard
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Wide beam	LL122X	Standard
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 WH	LED160S	-	2 units	6 pcs	Very wide beam	LL120X	Standard
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL122X	Standard
910925864066	LL121X LED80S/840 1x PSD VWB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Very wide beam	LL121X	Standard
910925864067	LL122X LED80S/840 1x PSD NB 7X2.5 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL122X	Standard
910925864068	LL121X LED80S/840 1x PSU MB 7 EL3 WH	LED80S	-	1 unit	3 pcs	Medium beam	LL121X	Standard
910925864069	LL120X LED160S/865 1x PSD MB 7 WH	LED160S	-	1 unit	6 pcs	Medium beam	LL120X	Standard
910925864070	LL120X LED160S/865 2x PSU MB 5 WH	LED160S	-	2 units	6 pcs	Medium beam	LL120X	Standard
910925864071	LL121X LED80S/840 1x PSD NB 9 EL3 WH	LED80S	-	1 unit	3 pcs	Narrow beam	LL121X	Standard
910925864629	LL121X LED76S/830 PSU WB TW3 SMB WH	-	-	1 unit	-	-	LL121X	-
910925864630	LL121X LED76S/830 PSU WB EL3 TW3 WH	-	-	1 unit	-	-	LL121X	-
910925864646	LL121X LED80S/840 PSD WB WH KIT	-	-	1 unit	-	-	LL121X	-
910925864647	LL121X LED80S/840 PSD NB WH KIT	-	-	1 unit	-	-	LL121X	-
910925863969	LL120X LED150S/840 1x PSD O 7 WH	LED150S	-	1 unit	6 pcs	-	LL120X	Standard
910925864022	LL120X LED150S/865 2x PSU O 5 WH	LED150S	-	2 units	6 pcs	-	LL120X	Standard
910925864540	LL120X LED150S/840 1x PSD PCO 7 WH	-	-	1 unit	-	-	LL120X	-
910925864541	LL120X LED150S/840 2x PSD PCO 7 VLC	-	-	2 units	-	-	LL120X	-
910925864542	LL121X LED75S/840 1x PSD PCO 7 WH	-	-	1 unit	-	-	LL121X	-
910925864543	LL120X LED150S/840 2x PSU PCO 5 WH	-	-	2 units	-	-	LL120X	-
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	-	-	1 unit	-	-	LL121X	-
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	-	-	1 unit	-	-	LL121X	-
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	-	-	1 unit	-	-	LL121X	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	4500 lm

CoreLine Trunking

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	4500 lm
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	4500 lm
910925682927	LL120X LED90S/840 2x PSU DA20 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925682933	LL120X LED90S/840 2x PSD NB 7 VLC WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925682946	LL121X LED45S/840 1x PSD DA20 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	4500 lm
910925682947	LL120X LED90S/840 2x PSD DA20 7 VLC WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	4500 lm
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925772904	LL120X LED90S/840	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	2x PSD WB 7 VLC WH				
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	4500 lm
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863327	LL120X LED90S/840 1x PSU A 5 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863335	LL120X LED90S/840 1x PSU A 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863336	LL120X LED90S/840 1x PSU VWB 7 WH	(0.38, 0.38) SDCM <3	4000 K	141 lm/W	9000 lm
910925863338	LL120X LED90S/865	(0.31, 0.33) SDCM <3	6500 K	141 lm/W	9000 lm

CoreLine Trunking

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	1x PSU WB 7 WH				
910925863330	LL120X LED84S/840	(0.38, 0.38) SDCM <3	4000 K	131 lm/W	8400 lm
	1x PSU O 7 WH				
910925863340	LL120X LED84S/865	(0.31, 0.33) SDCM <3	6500 K	131 lm/W	8400 lm
	1x PSU O 5 WH				
910925863968	LL120X LED150S/840	(0.38, 0.38) SDCM <3	4000 K	139 lm/W	15000 lm
	2x PSD O 7 VLC WH				
910925863979	LL120X LED150S/840	(0.38, 0.38) SDCM <3	4000 K	139 lm/W	15000 lm
	2x PSU O 5 WH				
910925863981	LL121X LED75S/840 1x	(0.38, 0.38) SDCM <3	4000 K	139 lm/W	7500 lm
	PSD O 7 WH				
910925863957	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
	PSU WB SMB WH KIT				
910925863958	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
	PSU NB SMB WH KIT				
910925863959	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
	PSU WB TW3 SMB WH KIT				
910925863960	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	PSU WB SMB WH KIT				
910925863961	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	PSU NB SMB WH KIT				
910925863962	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
	PSU NB TW3 SMB WH KIT				
910925863963	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	PSU WB TW3 SMB WH KIT				
910925863964	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU NB TW3 SMB WH KIT				
910925863965	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSD WB 7X2.5 VLC W				
910925863966	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSD WB 7 VLC WH				
910925863967	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSU WB 5 WH				
910925863970	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSU MB 5 WH				
910925863971	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
	1x PSD WB 7 WH				
910925863972	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSU DA20 5 WH				
910925863973	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
	1x PSU WB 5 WH				
910925863974	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	1x PSD WB 7 WH				
910925863975	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSU NB 5 WH				
910925863976	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	1x PSD WB 7X2.5 WH				
910925863977	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSD MB 7 VLC WH				
910925863978	LL120X LED160S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
	2x PSD WB 9 VLC WH				

CoreLine Trunking

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863993	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	1x PSU DA20 5 WH				
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	(0.38, 0.38) SDCM <3	4000 K	143 lm/W	8000 lm
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm

CoreLine Trunking

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864009	LL120X LED160S/840 2x PSU A 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	(0.38, 0.38) SDCM <3	4000 K	143 lm/W	8000 lm
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864019	LL121X LED80S/840 1x PSU A 5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864020	LL120X LED152S/830 2x PSU A 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	(0.38, 0.38) SDCM <3	6500 K	148 lm/W	16000 lm
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	(0.38, 0.38) SDCM <3	6500 K	148 lm/W	16000 lm
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	15200 lm
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864035	LL121X LED80S/840 1x PSD A 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864037	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm

CoreLine Trunking

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	1x PSU WB 7 WH				
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	(0.38, 0.38) SDCM <3	6500 K	148 lm/W	16000 lm
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	(0.38, 0.38) SDCM <3	6500 K	148 lm/W	8000 lm
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	(0.38, 0.38) SDCM <3	3000 K	136 lm/W	7600 lm
910925864043	LL121X LED76S/830 1x PSU A 5 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	(0.38, 0.38) SDCM <3	4000 K	143 lm/W	8000 lm
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	(0.38, 0.38) SDCM <3	4000 K	143 lm/W	8000 lm
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864053	LL121X LED76S/830 1x PSD A 7 WH	(0.38, 0.38) SDCM <3	3000 K	141 lm/W	7600 lm
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	(0.38, 0.38) SDCM <3	6500 K	148 lm/W	8000 lm
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 VLC	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	16000 lm
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm
910925864066	LL121X LED80S/840	(0.38, 0.38) SDCM <3	4000 K	148 lm/W	8000 lm

CoreLine Trunking

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864067	1x PSD VWB 7X2.5 WH				
	LL122X	(0.38, 0.38)	4000 K	148 lm/W	8000 lm
910925864068	LED80S/840 1x PSD NB 7X2.5 WH	SDCM <3			
	LL121X	(0.38, 0.38)	4000 K	143 lm/W	8000 lm
910925864069	LED80S/840 1x PSU MB 7 EL3 WH	SDCM <3			
	LL120X	(0.38, 0.38)	6500 K	148 lm/W	16000 lm
910925864070	LED160S/865 1x PSD MB 7 WH	SDCM <3			
	LL120X	(0.38, 0.38)	6500 K	148 lm/W	16000 lm
910925864071	LED160S/865 2x PSU MB 5 WH	SDCM <3			
	LL121X	(0.38, 0.38)	4000 K	143 lm/W	8000 lm
910925864629	LED80S/840 1x PSD NB 9 EL3 WH	SDCM <3			
	LL121X	(0.38, 0.38)	3000 K	141 lm/W	7600 lm
910925864630	LED76S/830 PSU WB TW3 SMB WH KIT	SDCM <3			
	LL121X	(0.38, 0.38)	3000 K	141 lm/W	7600 lm
910925864646	LED76S/830 PSU WB EL3 TW3 WH KIT	SDCM <3			
	LL121X	(0.38, 0.38)	4000 K	148 lm/W	8000 lm
910925864647	LED80S/840 PSD WB WH KIT	SDCM <3			
	LL121X	(0.38, 0.38)	4000 K	148 lm/W	8000 lm
	LED80S/840 PSD NB WH KIT	SDCM <3			
	LL121X	(0.38, 0.38)	4000 K	148 lm/W	8000 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Luminous flux tolerance	Initial input power
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	+/-7%	64 W
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	+/-7%	32 W
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	+/-7%	64 W
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	+/-7%	32 W
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	+/-7%	64 W
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	+/-7%	32 W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925863969	LL120X	(0.38, 0.38)	4000 K	139 lm/W	15000 lm
	LED150S/840 1x PSD O 7 WH	SDCM <3			
910925864022	LL120X	(0.38, 0.38)	6500 K	139 lm/W	15000 lm
	LED150S/865 2x PSU O 5 WH	SDCM <3			
910925864540	LL120X	(0.38, 0.38)	4000 K	120 lm/W	15000 lm
	LED150S/840 1x PSD PCO 7 WH	SDCM <3			
910925864541	LL120X	(0.38, 0.38)	4000 K	120 lm/W	15000 lm
	LED150S/840 2x PSD PCO 7 VLC WH	SDCM <3			
910925864542	LL121X	(0.38, 0.38)	4000 K	120 lm/W	7500 lm
	LED75S/840 1x PSD PCO 7 WH	SDCM <3			
910925864543	LL120X	(0.38, 0.38)	4000 K	120 lm/W	15000 lm
	LED150S/840 2x PSU PCO 5 WH	SDCM <3			
910925864544	LL121X	(0.38, 0.38)	4000 K	120 lm/W	7500 lm
	LED75S/840 1x PSU PCO 5 WH	SDCM <3			
910925864545	LL121X	(0.38, 0.38)	4000 K	120 lm/W	7500 lm
	LED75S/840 1x PSD PCO 9 EL3 WH	SDCM <3			
910925864546	LL121X	(0.38, 0.38)	4000 K	120 lm/W	7500 lm
	LED75S/840 1x PSU PCO 7 EL3 WH	SDCM <3			

CoreLine Trunking

Order Code	Full Product Name	Luminous flux tolerance	Initial input power
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	+/-7%	32 W
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	+/-7%	64 W
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	+/-7%	64 W
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	+/-7%	64 W
910925772904	LL120X LED90S/840 2x PSD WB 7 VLC WH	+/-7%	64 W
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	+/-7%	32 W
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	+/-7%	64 W
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	+/-7%	64 W
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	+/-7%	64 W
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	+/-7%	64 W
910925863327	LL120X LED90S/840 1x PSU A 5 WH	+/-7%	64 W
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	+/-7%	64 W
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	+/-7%	64 W
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	+/-7%	64 W
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	+/-7%	64 W
910925863335	LL120X LED90S/840 1x PSU A 7 WH	+/-7%	64 W
910925863336	LL120X LED90S/840 1x PSU VWB 7 WH	+/-7%	64 W
910925863338	LL120X LED90S/865 1x PSU WB 7 WH	+/-7%	64 W
910925863330	LL120X LED84S/840 1x PSU O 7 WH	+/-7%	64 W
910925863340	LL120X LED84S/865 1x PSU O 5 WH	+/-7%	64 W
910925863968	LL120X LED150S/840 2x PSD O 7 VLC WH	+/-2%	108 W
910925863979	LL120X LED150S/840 2x PSU O 5 WH	+/-2%	108 W
910925863981	LL121X LED75S/840 1x PSD O 7 WH	+/-1%	54 W
910925863957	LL121X LED80S/840 PSU WB SMB WH KIT	+/-1%	54 W
910925863958	LL121X LED80S/840 PSU NB SMB WH KIT	+/-1%	54 W
910925863959	LL121X LED80S/840 PSU WB TW3 SMB WH KIT	+/-1%	54 W
910925863960	LL120X LED160S/840 PSU WB SMB WH KIT	+/-2%	108 W
910925863961	LL120X LED160S/840 PSU NB SMB WH KIT	+/-2%	108 W
910925863962	LL121X LED80S/840 PSU NB TW3 SMB WH KIT	+/-1%	54 W
910925863963	LL120X LED160S/840 PSU WB TW3 SMB WH KIT	+/-2%	108 W
910925863964	LL120X LED160S/840 PSU NB TW3 SMB WH KIT	+/-2%	108 W
910925863965	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W	+/-2%	108 W
910925863966	LL120X LED160S/840 2x PSD WB 7 VLC WH	+/-2%	108 W
910925863967	LL120X LED160S/840 2x PSU WB 5 WH	+/-2%	108 W
910925863970	LL120X LED160S/840 2x PSU MB 5 WH	+/-2%	108 W
910925863971	LL121X LED80S/840 1x PSD WB 7 WH	+/-1%	54 W

Order Code	Full Product Name	Luminous flux tolerance	Initial input power
910925863972	LL120X LED160S/840 2x PSU DA20 5 WH	+/-2%	108 W
910925863973	LL121X LED80S/840 1x PSU WB 5 WH	+/-1%	54 W
910925863974	LL120X LED160S/840 1x PSD WB 7 WH	+/-2%	108 W
910925863975	LL120X LED160S/840 2x PSU NB 5 WH	+/-2%	108 W
910925863976	LL120X LED160S/840 1x PSD WB 7X2.5 WH	+/-2%	108 W
910925863977	LL120X LED160S/840 2x PSD MB 7 VLC WH	+/-2%	108 W
910925863978	LL120X LED160S/840 2x PSD WB 9 VLC WH	+/-2%	108 W
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	+/-1%	54 W
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	+/-1%	54 W
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	+/-2%	108 W
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	+/-2%	108 W
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	+/-2%	108 W
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	+/-2%	108 W
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	+/-2%	108 W
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	+/-2%	108 W
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	+/-2%	108 W
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	+/-1%	54 W
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	+/-2%	108 W
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	+/-2%	108 W
910925863993	LL121X LED80S/840 1x PSU DA20 5 WH	+/-1%	54 W
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	+/-2%	108 W
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	+/-2%	108 W
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	+/-2%	108 W
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	+/-1%	54 W
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	+/-2%	108 W
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	+/-1%	54 W
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	+/-1%	54 W
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	+/-1%	56 W
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	+/-1%	54 W
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	+/-1%	54 W
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	+/-1%	54 W
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	+/-1%	54 W
910925864009	LL120X LED160S/840 2x PSU A 5 WH	+/-2%	108 W
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	+/-1%	54 W
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	+/-1%	54 W
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	+/-1%	54 W
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	+/-1%	56 W

CoreLine Trunking

Order Code	Full Product Name	Luminous flux tolerance	Initial input power
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	+/-2%	108 W
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	+/-2%	108 W
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	+/-1%	54 W
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	+/-2%	108 W
910925864019	LL121X LED80S/840 1x PSU A 5 WH	+/-1%	54 W
910925864020	LL120X LED152S/830 2x PSU A 5 WH	+/-2%	108 W
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	+/-2%	108 W
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	+/-1%	54 W
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	+/-1%	54 W
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	+/-1%	54 W
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	+/-1%	54 W
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	+/-2%	108 W
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	+/-1%	54 W
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	+/-1%	54 W
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	+/-2%	108 W
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	+/-1%	54 W
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	+/-1%	54 W
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	+/-1%	54 W
910925864035	LL121X LED80S/840 1x PSD A 7 WH	+/-1%	54 W
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	+/-1%	54 W
910925864037	LL121X LED80S/840 1x PSU WB 7 WH	+/-1%	54 W
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	+/-2%	108 W
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	+/-1%	54 W
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	+/-1%	54 W
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	+/-2%	108 W
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	+/-1%	56 W
910925864043	LL121X LED76S/830 1x PSU A 5 WH	+/-1%	54 W
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	+/-1%	56 W
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	+/-1%	54 W
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	+/-1%	56 W
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	+/-2%	108 W
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	+/-1%	54 W
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	+/-1%	54 W
910925864053	LL121X LED76S/830 1x PSD A 7 WH	+/-1%	54 W
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	+/-2%	108 W

Order Code	Full Product Name	Luminous flux tolerance	Initial input power
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	+/-1%	54 W
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	+/-1%	54 W
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	+/-1%	54 W
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	+/-2%	108 W
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	+/-1%	54 W
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	+/-1%	54 W
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	+/-1%	54 W
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	+/-1%	54 W
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 VLC	+/-2%	108 W
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	+/-1%	54 W
910925864066	LL121X LED80S/840 1x PSD VWB 7X2.5 WH	+/-1%	54 W
910925864067	LL122X LED80S/840 1x PSD NB 7X2.5 WH	+/-1%	54 W
910925864068	LL121X LED80S/840 1x PSU MB 7 EL3 WH	+/-1%	56 W
910925864069	LL120X LED160S/865 1x PSD MB 7 WH	+/-2%	108 W
910925864070	LL120X LED160S/865 2x PSU MB 5 WH	+/-2%	108 W
910925864071	LL121X LED80S/840 1x PSD NB 9 EL3 WH	+/-1%	56 W
910925864629	LL121X LED76S/830 PSU WB TW3 SMB WH KIT	+/-1%	54 W
910925864630	LL121X LED76S/830 PSU WB EL3 TW3 WH KIT	+/-1%	54 W
910925864646	LL121X LED80S/840 PSD WB WH KIT	+/-1%	54 W
910925864647	LL121X LED80S/840 PSD NB WH KIT	+/-1%	54 W
910925863969	LL120X LED150S/840 1x PSD O 7 WH	+/-2%	108 W
910925864022	LL120X LED150S/865 2x PSU O 5 WH	+/-2%	108 W
910925864540	LL120X LED150S/840 1x PSD PCO 7 WH	+/-2%	126 W
910925864541	LL120X LED150S/840 2x PSD PCO 7 VLC WH	+/-2%	126 W
910925864542	LL121X LED75S/840 1x PSD PCO 7 WH	+/-2%	63 W
910925864543	LL120X LED150S/840 2x PSU PCO 5 WH	+/-2%	126 W
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	+/-2%	63 W
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	+/-2%	63 W
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	+/-2%	63 W

Mechanical and Housing

CoreLine Trunking

Order Code	Full Product Name	Color	Diameter
910925682908	LL120X LED90S/840 2x PSU NB 5 WH	White	-
910925682914	LL121X LED45S/840 1x PSU MB 5 WH	White	-
910925682915	LL120X LED90S/840 2x PSU MB 5 WH	White	-
910925682920	LL121X LED45S/840 1x PSU WB 5 WH	White	-
910925682921	LL120X LED90S/840 2x PSU WB 5 WH	White	-
910925682926	LL121X LED45S/840 1x PSU DA20 5 WH	White	-
910925682927	LL120X LED90S/840 2x PSU DA20 5 WH	White	-
910925682933	LL120X LED90S/840 2x PSD NB 7 VLC WH	White	-
910925682946	LL121X LED45S/840 1x PSD DA20 7 WH	White	-
910925682947	LL120X LED90S/840 2x PSD DA20 7 VLC WH	White	-
910925682955	LL121X LED45S/840 1x PSU NB 5 WH	White	-
910925682968	LL120X LED90S/840 2x PSU VWB 5 WH	White	-
910925683021	LL120X LED90S/840 2x PSD WB 9 VLC WH	White	-
910925683023	LL120X LED90S/840 2x PSD VWB 9 VLC WH	White	-
910925772904	LL120X LED90S/840 2x PSD WB 7 VLC WH	White	-
910925802903	LL121X LED45S/840 1x PSD WB 7 WH	White	-
910925863110	LL120X LED90S/840 1x PSD WB 9 WH	White	-
910925863324	LL120X LED90S/840 1x PSU NB 5 WH	White	-
910925863325	LL120X LED90S/840 1x PSU MB 5 WH	White	-
910925863326	LL120X LED90S/840 1x PSU DA20 5 WH	White	-
910925863327	LL120X LED90S/840 1x PSU A 5 WH	White	-
910925863331	LL120X LED90S/840 1x PSU DA20 7 WH	White	-
910925863332	LL120X LED90S/840 1x PSU MB 7 WH	White	-
910925863333	LL120X LED90S/840 1x PSU NB 7 WH	White	-
910925863334	LL120X LED90S/840 1x PSU WB 7 WH	White	-
910925863335	LL120X LED90S/840 1x PSU A 7 WH	White	-
910925863336	LL120X LED90S/840 1x PSU VWB 7 WH	White	-
910925863338	LL120X LED90S/865 1x PSU WB 7 WH	White	-
910925863330	LL120X LED84S/840 1x PSU O 7 WH	White	-
910925863340	LL120X LED84S/865 1x PSU O 5 WH	White	-
910925863968	LL120X LED150S/840 2x PSD O 7 VLC WH	White	-
910925863979	LL120X LED150S/840 2x PSU O 5 WH	White	-
910925863981	LL121X LED75S/840 1x PSD O 7 WH	White	-
910925863957	LL121X LED80S/840 PSU WB SMB WH KIT	White	-
910925863958	LL121X LED80S/840 PSU NB SMB WH KIT	White	-
910925863959	LL121X LED80S/840 PSU WB TW3 SMB WH KIT	White	-
910925863960	LL120X LED160S/840 PSU WB SMB WH KIT	White	-
910925863961	LL120X LED160S/840 PSU NB SMB WH KIT	White	-
910925863962	LL121X LED80S/840 PSU NB TW3 SMB WH KIT	White	-
910925863963	LL120X LED160S/840 PSU WB TW3 SMB WH KIT	White	-
910925863964	LL120X LED160S/840 PSU NB TW3 SMB WH KIT	White	-
910925863965	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W	White	-
910925863966	LL120X LED160S/840 2x PSD WB 7 VLC WH	White	-
910925863967	LL120X LED160S/840 2x PSU WB 5 WH	White	-
910925863970	LL120X LED160S/840 2x PSU MB 5 WH	White	-
910925863971	LL121X LED80S/840 1x PSD WB 7 WH	White	-
910925863972	LL120X LED160S/840 2x PSU DA20 5 WH	White	-
910925863973	LL121X LED80S/840 1x PSU WB 5 WH	White	-
910925863974	LL120X LED160S/840 1x PSD WB 7 WH	White	-
910925863975	LL120X LED160S/840 2x PSU NB 5 WH	White	-
910925863976	LL120X LED160S/840 1x PSD WB 7X2.5 WH	White	-
910925863977	LL120X LED160S/840 2x PSD MB 7 VLC WH	White	-

Order Code	Full Product Name	Color	Diameter
910925863978	LL120X LED160S/840 2x PSD WB 9 VLC WH	White	-
910925863980	LL121X LED76S/830 1x PSU WB 5 WH	White	-
910925863982	LL121X LED80S/840 1x PSU MB 5 WH	White	-
910925863983	LL120X LED152S/830 2x PSU WB 5 WH	White	-
910925863984	LL120X LED160S/840 2x PSD VWB 7 VLC WH	White	-
910925863985	LL120X LED152S/830 2x PSU VWB 5 WH	White	-
910925863986	LL120X LED160S/840 1x PSD NB 7 WH	White	-
910925863987	LL120X LED160S/840 1x PSD MB 7 WH	White	-
910925863988	LL120X LED152S/830 2x PSU DA20 5 WH	White	-
910925863989	LL120X LED160S/840 2x PSD NB 9 VLC WH	White	-
910925863990	LL121X LED80S/840 1x PSD WB 7X2.5 WH	White	-
910925863991	LL120X LED160S/840 2x PSU WB 7 WH	White	-
910925863992	LL120X LED160S/840 2x PSD NB 7 VLC WH	White	-
910925863993	LL121X LED80S/840 1x PSU DA20 5 WH	White	-
910925863994	LL120X LED152S/830 2x PSD WB 7 VLC WH	White	-
910925863995	LL120X LED152S/830 2x PSU MB 5 WH	White	-
910925863996	LL120X LED160S/840 2x PSU VWB 5 WH	White	-
910925863997	LL121X LED76S/830 1x PSD WB 7 WH	White	-
910925863998	LL120X LED160S/840 2x PSD A 7X2.5 VLC WH	White	-
910925863999	LL121X LED80S/840 1x PSD NB 7 WH	White	-
910925864002	LL121X LED80S/840 1x PSU VWB 5 WH	White	-
910925864003	LL121X LED80S/840 1x PSU WB 7 EL3 WH	White	-
910925864004	LL121X LED80S/840 1x PSD MB 7 WH	White	-
910925864005	LL121X LED80S/840 1x PSD WB 9 WH	White	-
910925864007	LL121X LED80S/840 1x PSU NB 5 WH	White	-
910925864008	LL121X LED80S/840 1x PSD NB 9 WH	White	-
910925864009	LL120X LED160S/840 2x PSU A 5 WH	White	-
910925864010	LL122X LED80S/840 1x PSU WB 5 WH	White	-
910925864011	LL122X LED80S/840 1x PSU VWB 5 WH	White	-
910925864012	LL121X LED76S/830 1x PSU MB 5 WH	White	-
910925864013	LL121X LED80S/840 1x PSD WB 9 EL3 WH	White	-
910925864014	LL120X LED160S/840 2x PSD MB 9 VLC WH	White	-
910925864016	LL120X LED160S/840 2x PSD DA20 7 VLC WH	White	-
910925864017	LL121X LED80S/840 1x PSD DA20 7 WH	White	-
910925864018	LL120X LED160S/840 2x PSD A 7 VLC WH	White	-
910925864019	LL121X LED80S/840 1x PSU A 5 WH	White	-
910925864020	LL120X LED152S/830 2x PSU A 5 WH	White	-
910925864021	LL120X LED160S/865 2x PSD VWB 7 VLC WH	White	-
910925864023	LL121X LED80S/840 1x PSD MB 9 WH	White	-
910925864024	LL121X LED80S/840 1x PSD VWB 7 WH	White	-
910925864025	LL121X LED80S/840 1x PSU MB 7 WH	White	-
910925864026	LL122X LED80S/840 1x PSD VWB 7 WH	White	-
910925864028	LL120X LED160S/865 2x PSU WB 5 WH	White	-
910925864029	LL122X LED80S/840 1x PSD WB 9 WH	White	-
910925864030	LL121X LED80S/840 1x PSU WB 7X2.5 WH	White	-
910925864031	LL120X LED152S/830 2x PSD DA20 7 VLC WH	White	-
910925864032	LL121X LED76S/830 1x PSU DA20 5 WH	White	-
910925864033	LL121X LED80S/840 1x PSU NB 7X2.5 WH	White	-
910925864034	LL121X LED76S/830 1x PSU VWB 5 WH	White	-
910925864035	LL121X LED80S/840 1x PSD A 7 WH	White	-
910925864036	LL122X LED76S/830 1x PSU VWB 7 WH	White	-
910925864037	LL121X LED80S/840 1x PSU WB 7 WH	White	-

CoreLine Trunking

Order Code	Full Product Name	Color	Diameter
910925864038	LL120X LED160S/865 2x PSD MB 7 VLC WH	White	-
910925864039	LL121X LED76S/830 1x PSD WB 9 WH	White	-
910925864040	LL121X LED80S/865 1x PSD WB 7 WH	White	-
910925864041	LL120X LED160S/840 2x PSU MB 7 WH	White	-
910925864042	LL121X LED76S/830 1x PSU VWB 7 EL3 WH	White	-
910925864043	LL121X LED76S/830 1x PSU A 5 WH	White	-
910925864045	LL121X LED80S/840 1x PSU DA20 7 EL3 WH	White	-
910925864046	LL121X LED80S/840 1x PSD A 7X2.5 WH	White	-
910925864047	LL121X LED80S/840 1x PSU NB 7 EL3 WH	White	-
910925864048	LL120X LED160S/840 2x PSU NB 7 WH	White	-
910925864049	LL121X LED76S/830 1x PSU VWB 7 WH	White	-
910925864051	LL121X LED80S/840 1x PSU NB 7 WH	White	-
910925864053	LL121X LED76S/830 1x PSD A 7 WH	White	-
910925864055	LL120X LED160S/840 2x PSU VWB 7 WH	White	-
910925864056	LL121X LED80S/840 1x PSU VWB 7 WH	White	-
910925864057	LL121X LED80S/865 1x PSD MB 9 WH	White	-
910925864058	LL122X LED80S/840 1x PSU WB 5X2.5 WH	White	-
910925864059	LL120X LED160S/840 2x PSU VWB 5X2.5 WH	White	-
910925864060	LL122X LED80S/840 1x PSU VWB 5X2.5 WH	White	-
910925864061	LL121X LED80S/840 1x PSU VWB 5X2.5 WH	White	-
910925864062	LL122X LED80S/840 1x PSU NB 5X2.5 WH	White	-
910925864063	LL122X LED80S/840 1x PSD WB 7X2.5 WH	White	-

Order Code	Full Product Name	Color	Diameter
910925864064	LL120X LED160S/840 2x PSD VWB 7X2.5 VLC	White	-
910925864065	LL122X LED80S/840 1x PSD VWB 7X2.5 WH	White	-
910925864066	LL121X LED80S/840 1x PSD VWB 7X2.5 WH	White	-
910925864067	LL122X LED80S/840 1x PSD NB 7X2.5 WH	White	-
910925864068	LL121X LED80S/840 1x PSU MB 7 EL3 WH	White	-
910925864069	LL120X LED160S/865 1x PSD MB 7 WH	White	-
910925864070	LL120X LED160S/865 2x PSU MB 5 WH	White	-
910925864071	LL121X LED80S/840 1x PSD NB 9 EL3 WH	White	-
910925864629	LL121X LED76S/830 PSU WB TW3 SMB WH KIT	White	-
910925864630	LL121X LED76S/830 PSU WB EL3 TW3 WH KIT	White	-
910925864646	LL121X LED80S/840 PSD WB WH KIT	White	-
910925864647	LL121X LED80S/840 PSD NB WH KIT	White	-
910925863969	LL120X LED150S/840 1x PSD O 7 WH	White	-
910925864022	LL120X LED150S/865 2x PSU O 5 WH	White	-
910925864540	LL120X LED150S/840 1x PSD PCO 7 WH	white	-
910925864541	LL120X LED150S/840 2x PSD PCO 7 VLC WH	white	-
910925864542	LL121X LED75S/840 1x PSD PCO 7 WH	white	-
910925864543	LL120X LED150S/840 2x PSU PCO 5 WH	white	-
910925864544	LL121X LED75S/840 1x PSU PCO 5 WH	white	-
910925864545	LL121X LED75S/840 1x PSD PCO 9 EL3 WH	white	-
910925864546	LL121X LED75S/840 1x PSU PCO 7 EL3 WH	white	-

