



Accessories - completing your Luminaire Based System

Luminaire Based Accessoires

Luminaire Based Accessories cover a generic range of products which can be used to extend functionality and/or simplify the design-in of our luminaire based systems.

Avantages

- Luminaire based accessories offer the possibility to extend the ActiLume family
- Accessories are clips, covers, rings and extension sensors
- Clips will ease the installation of sensors by making it possible to clip them onto the lamp
- Covers and rings are to obtain the same outer dimensions across the ActiLume family sensors and extension sensors
- Ease of installation

Fonctions

- Philips ActiLume systems are DALI- or 1-10V based lighting control system designed for maximum comfort and energy savings of up to 75% (in fully automatic mode and when used in combination with Philips HF-Regulator Touch and DALI or 1-10V ballasts)

Application


- Luminaire based accessories are designed for all ActiLume systems used in office applications, from open-plan to cell offices, lobbies or toilets, and from corridors to small meeting rooms

Luminaire Based Accessoires

Versions



Schéma dimensionnel



Product

LCA8005/05 ActiLume Mounting Clip 50 W

Product

LCA8005/00 ActiLume Mounting Clip 50pce

Luminaire Based Accessoires

Détails sur le produit

LCA8005/0x ActiLume mounting clip
for use in luminaire

