



LuxSense - simple daylight harvesting

LuxSense

LuxSense is a DayLight Regulation option (DLR) for luminaires equipped with a Philips HFR ballast. The sensor measures the reflected light coming from the surface below. It dims down the lamp output when the light level exceeds the required light level defined by the light sensor set point. LuxSense can be installed in the luminaire by attaching it to the lamp with a lamp clip. LuxSense is available as a complete set with a sensor and a lamp clip: LRL1220 TL-D for TLD lamps and LRL1220 TL5 for T5 lamps.

Benefits

- A simple Daylight Regulation device which can easily be fitted in a 1-10V luminaire
- Offers energy saving opportunities when installed near windows


Features

- LuxSense is connected to the 1-10 V_{DC} control input of the HF-R ballast
- LuxSense dims light down to the minimum level of the ballast (3% for the Philips HF-R ballast)
- LuxSense is calibrated for use in a standard office situation with 600 lux installed and 500 lux required
- If needed, LuxSense can be manually adjusted by a rotating diaphragm to adjust the set point. The sensitivity of the sensor can be changed within a range from 1/3 to 3
- The new set point can be copied for all LuxSense luminaires with similar daylight and reflection conditions
- LuxSense can regulate up to 20 luminaires equipped with Philips HF-R ballasts


Application

- LuxSense is designed for all office applications
- LuxSense is designed for average ceiling heights of between 2.5 and 3 m
- LuxSense can be used alone or in combination with other control products in order to add the daylight regulation functionality (e.g. combination of LuxSense with OccuSwitch)

Versions



Dimensional drawing



Product
LRL1220 TL-D
LRL1220 TL5

