



Chronosense - the flexible stand-alone dimming solution

Chronosense

Luminaire based, stand-alone controller for magnetic ballasts up to 600 W. Suitable for outdoor applications like roads, streets, residential and area lighting. Step-dim schedule is created using 5 dip switches, dim schedule is flexible between 4 and 9 hours around the midpoint of the night.

Benefits

- Energy savings of up to 30%
- Stand-alone, no commissioning, no operational costs
- Reduced light nuisance

Features

- Simple dip switch settings to set/reset the dim period
- Small size with smart connectors for easy mounting
- Midpoint of the night calculation guarantees maximum savings

Application

- Each Chronosense can control a driver/lamp combination in a stand-alone manner
- Designed for use in residential, street, area and road lighting applications, including parking lots, ports, train stations and industrial complexes
- The design of Chronosense is optimized for mounting in a luminaire or gear tray
- Chronosense is designed to interact with any magnetic ballast up to 600 W

Versions

