



# MBN100

## MBN100

With the MBN 100 and MBN200 downlights, Philips adds to the convenience, performance and reliability of downlights and a host of features designed to create an array of appealing effects and ambiances for your retail outlets. These recessed adjustable downlights offer a choice of two designs, round or square, and are suited for MASTER Color CDM-T lamps.

### Features

- Die-cast aluminium housing, solid and durable, excellent heat dissipating effect
- Separated gear box to reduce the bearing of ceiling and good for heat dissipating
- Orientation: 52° vertical and horizontal 360° adjustable

### Application

- Small independent food/non-food shops
- Discount stores, hyper-/supermarkets, do-it-yourself shops
- High-end fashion shops, boutiques
- Department stores, fashion shops

### Versions

