



M/QCS145

MCS/QCS145 C

Professional surface mounted downlights complimenting the family of the 145 range. Complete with a very efficient highly-polished reflector in silver aluminium finish. Suitable for PAR reflector halogen, the range comes with a standard white decorative plastic ring. Accessories are common and interchangeable for the entire 145 range. Colour options upon request.

Features

- Compact design with “3 in 1” concept of integrating the lamp-reflector-control gear
- Modular concept with same diameter allows a consistent appearance and interchangeable accessories and components e.g. reflectors to cater to different lighting needs
- Extruded aluminium housing creates a compact and sturdy architecture to interface with the different accessories
- Double ring structure – the outer plastic ring allows colour selections and the inner frame is made of die-cast aluminium
- Quick “click and twist” design of base plate makes the installation easy and convenient

Application

- Mixed use shopping centres
- Corridors
- Department stores - general lighting
- High-end fashion shops and boutiques
- Restaurants, cafeterias and hotels
- Museum display, public buildings and waiting areas
- Transport buildings eg airport terminals and interchanges
- Small offices and conference rooms

MCS/QCS145 C

Versions

