



# UnicOne Projector – Powerful effects

## UnicOne Projector Mini MCS/MRS551 C

The UnicOne Projector range offers powerful lighting accents in a small, appealing package, making it ideal for retail and hospitality areas. The Projector adds a sophisticated adjustment rod and hinge to the unique UnicOne design concept. Thanks to its simple design, the UnicOne Projector can be integrated into a variety of environments. The range is designed around the most efficient Elite compact HID and MASTER halogen lamps. The Micro version incorporates MASTERColour CDM-Tm Mini 20/35 W and Masterline halogen lamps, while the Mini version offers higher lumen packages in a compact housing and different accessories. The MiniR111 provides not only strong lighting effects but also good glare control. With such a full range, you certainly have no shortage of choice!

### Benefits

- Simple design ensures versatility in application
- Designed around highly efficient Elite compact HID and MASTER halogen lamps
- Full range offering extensive choice

### Features

- Micro version – MASTERColour CDM-Tm Mini 20/35 W and Masterline halogen lamps
- Mini version i– MASTERColour CDM-Tc Elite 35/70 W and Masterline halogen lamps
- MiniR111 version – CDM-R111 and Masterline 111/60 W lamps
- Adjustment rod and hinge

### Application

- Retail
- Museums
- Exhibition areas
- Public areas

### Specifications

## UnicOne Projector Mini MCS/MRS551 C

<b>Type</b>	MRS551 (Mini, 1-circuit track version)
	MCS551 (Mini, baseplate version)
	MRS/LRS553 (Mini R111, 1-circuit track version)
	MCS/LCS553 (Mini R111, baseplate version)
<b>Light source</b>	MRS/MCS551
	- HID: 1 x MASTERColour CDM-TC Elite / G8.5 / 35, 70 W
	MRS/MCS553
	- HID: 1 x MASTERColour CDM-R111 / GX8.5 / 20, 35, 70 W
	LRS/LCS553
	- Halogen: 1 x MASTERLine 111 / G53 / 60 W
<b>Lamp beam angle</b>	MASTERLine and MASTERLine 111: 8, 24, 36°
<b>Lamp included</b>	No
<b>Lamp position</b>	Vertical
<b>Light distribution</b>	Direct (D)
<b>Ballast</b>	Electronic, High Frequency 220-240 V / 50-60 Hz:
	- Electronic (EB) for HID lamp version

<b>Transformer</b>	Electronic (ET) for halogen lamp version
<b>Optic</b>	Beam angle 12 to 36° (12-36)
	Reflector narrow beam 12° (R-NB12)
	Reflector medium beam 24° (R-MB24)
	Reflector medium beam 36° (R-MB36)
<b>Connection</b>	3-pole mains
<b>Material</b>	Housing: die-cast aluminum
	Glass, tempered
<b>Color</b>	White (WH), black (BK) or grey (GR)
<b>Installation</b>	Direct on ceiling; baseplate with connection point (BA)
	1-circuit track mounted
<b>Accessories</b>	Protection glass, sculptural lens, UV filters, honey comb louvres and barndoors

### Versions



MRS551 CDM EB 1C WH



MRS551 CDM EB 1C GR



# UnicOne Projector Mini MCS/MRS551 C

## Approval and Application

Ingress protection code	IP20
-------------------------	------

## General Information

Gear	EB
Lamp family code	CDM-TC
Lamp power	70 W
Number of light sources	1 pc

## General Information

Order Code	Full Product Name	Optic type
911401033680	MRS551 C 1xCDM-TC70W EB 36 1C WH	Beam angle 36°

Order Code	Full Product Name	Optic type
911401033980	MRS551 C 1xCDM-TC70W EB 24 1C GR	Beam angle 24°

## Mechanical and Housing

Order Code	Full Product Name	Color
911401033680	MRS551 C 1xCDM-TC70W EB 36 1C WH	White

Order Code	Full Product Name	Color
911401033980	MRS551 C 1xCDM-TC70W EB 24 1C GR	Gray

