



Versebay Elite – highly efficient high-bay system solution

VerseBay Elite MPK518

Manufacturing customers want energy-efficient lighting solutions to help ensure their factories are green. Versebay Elite is a high-bay luminaire incorporating high-efficacy CDM Elite lamp technology, as well as extremely efficient gear, which almost halves energy consumption compared with a conventional metal-halide solution. It also provides brilliant lighting performance with excellent color rendering. Versebay Elite's choice of wide and narrow beams makes it suitable for a variety of applications. The luminaire's robust construction and high ingress protection also mean it can be deployed in the most demanding, heavy-duty working environments.

Преимущества

- Energy-efficient
- Excellent lighting performance
- Robust, versatile solution

Характеристики

- CDM Elite efficacy 115-120 lm/W
- PrimoVision driver efficacy 92%, with good thermal control; power factor over 0.98
- Well-designed optic; fixture light output ratio 76%
- Color rendering > 90
- IP65

Применение

- Industry
- Retail

VerseBay Elite MPK518

Versions



Versebay Elite MPK518 highbay
luminaire

Сведения о продукте



Аксессуары



GPK518

Ordercode 911401504501



© 2018 Signify Holding Все права защищены. Signify никоим образом не гарантирует точность и полноту представленной здесь информации и не несет ответственности за любые действия, совершенные в этой связи.

Информация, представленная в данном документе, не является коммерческим предложением и не является частью какого-либо предложения или контракта, если иное не подтверждено Signify. Все товарные знаки являются собственностью компании Signify Holding или соответствующих владельцев.

www.lighting.philips.com

2018, Ноябрь 29 - Данные для изменения