



UnicOne Pendant – Stylish suspensions

UnicOne Pendant Micro MPK541 C

The UnicOne Pendant range allows you to decorate your interiors with very stylish suspensions while still enjoying the required lighting levels. This makes these luminaires suitable for use in, for example, reception halls, lobbies, supermarkets and other public areas. The Pendant series combines the refined UnicOne design style and details with a wide choice of best-in-class lamps and dedicated optics. Designed around MASTERColour CDM Tm Mini 20/35 W and Masterline halogen lamps, the UnicOne Pendant Micro versions feature a subtle conical lamp housing and a distinctive, square ceiling base, connected by sophisticated translucent cables.

Benefits

- Refined design style and details
- Wide choice of best-in-class lamps and dedicated optics

Features

- Conical lamp housing
- Square ceiling base
- Translucent cables

Application

- Retail
- Museums
- Exhibition areas
- Public areas

Specifications

Type	MPK541 (Micro, pendant, HID lamp version)	Light source	MPK541
	LPK541 (Micro, pendant, halogen lamp version)		- HID: 1 x MASTERColour CDM-Tm Mini / PGJ5 / 20, 35 W
			LPK541

UnicOne Pendant Micro MPK541 C

	- Halogen: 1 x MASTERLine ES / GU5.3 / 45 W
Lamp beam angle	MASTERLine ES: 8, 24, 36°
Lamp included	No
Lamp position	Vertical
Light distribution	Direct (D)
Ballast	Electronic, High Frequency 220-240 V / 50-60 Hz: - Electronic (EB) for HID lamp version
Transformer	Electronic (ET) for halogen lamp version
Optic	Beam angle 12 to 36° (12-36) Reflector narrow beam 12° (R-NB12) Reflector medium beam 24° (R-MB24) Reflector medium beam 36° (R-MB36)

Material	Housing: die-cast aluminum Glass, tempered
Color	White (WH)
Installation	Direct on ceiling; baseplate with connection point (BA) On 1-circuit track (1C)
Accessories	Protection glass, sculptural lens, UV filters, honey comb louvres and barndoors
Remarks	Delivered with protection glass

Versions

