



Smart Spot LCS/LRS/MRS070/071 – a reliable way to create outstanding lighting

Basic Spot MRS070

The affordable Smart Spot projector range is a reliable and flexible solution offering a choice of CDM and halogen lamps in various shapes and colors. Designed for operation in conjunction with the Smart Track family, it can be track-mounted or fixed on the ceiling. Smart Spot delivers a good accent lighting effect, making it suitable for projector applications in shops or art galleries. Its stylish design is ideal for integration in a fashion environment and ambience.

Benefits

- No worries about safety and reliability
- Easy to select and to use
- Affordable; low initial cost

Features

- CCC-certified; truly safe and reliable
- Choice of lamp types, designs and colors
- Stylish design; integrates perfectly into fashion ambience

Application

- Shopping areas
- Art galleries

Basic Spot MRS070

Versions



Operating and Electrical	
Maximum lamp power	MAX50
General Information	
Cap-Base	GU5.3
Compensation circuit	-
Gear	-
Number of light sources	1

Mechanical and Housing

Order Code	Full Product Name	Colour
911400895280	LRS070 1x MAX50W/12V-GU5.3 L65 WH	White

Order Code	Full Product Name	Colour
911400895380	LRS070 1x MAX50W/12V-GU5.3 L65 BK	Black

