



# MASTER LEDbulb – Elegance meets efficiency

## MASTER Plastic LEDbulbs

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

### Benefits

- Up to 80% energy saving compared with traditional incandescent lamps
- 85% energy saving compared with traditional incandescent lamps
- Easy (retrofit) replacement
- Easy (retrofit) replacement
- Lower maintenance costs

# MASTER Plastic LEDbulbs

## Features

- Dimmable
- Unique optical design allows for sparkling light
- Compatible with an extensive range of dimmers
- Dimmable
- Warm white light
- Compatible with an extensive range of dimmers
- Lifetime of 25,000 to 45,000 hours
- Warm white light
- UV- and IR-free light
- Lifetime of 25,000 hours
- UV- and IR-free light

## Application

- Hotels, restaurants, bars, cafés
- Hotels, restaurants, bars, cafés
- Lobbies, corridors, stairwells, reception areas
- Lobbies, corridors, stairwells, reception areas

## Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights



## Versions



LEDbulb MAS SLR1 A60 E27 CL 1

# MASTER Plastic LEDbulbs

## Dimensional drawing



Product	D	C
MAS LEDbulb DT 8-60W E27 A60 CL	60.5 mm	110 mm

