



MASTER LEDspot LV – The ideal solution for spot lighting

MASTER VALUE LEDspot LV

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Benefits

- Up to 80% energy saving compared with halogen lamp
- Up to 80% energy saving compared with halogen lamp
- · Broad compatibility with transformers
- · Broad compatibility with transformers
- Retrofittable with low-voltage MR16 halogen lamps with GU5.3 socket
- Suitable to retrofit with low-voltage halogen lamps covering GU5.3 and GU4 base types

Features

- · dimmable (the 7-35W and 10-50W versions)
- · Dimmable (6.5-35W versions)
- · patented intelligent driver
- · Innovative AirFlux technology for passive cooling, depending upon model
- · air movement mechanism (active fan cooling) with very low sound levels
- · Warm and cool white light
- · lifetime of 25,000 to 45,000 hours
- · Lifetime:
- · CRI90 (MR11 only)
- · 40.000 hours MASTER LED
- · 25,000 hours MASTER LED VALUE
- TransforMax technology to ensure compatibility with existing transformers (depending upon model)

Application

- Ideal for accent lighting in hotels, hospitals, shops and museums (e.g. floors, elevators, displays)
- Ideal for accent lighting in hotels, hospitals, shops and museums (e.g. floors, elevators, displays)

Warnings and Safety

- · Operating temperature range is between -20° C and 45° C ambient
- · Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights


Versions





MASTER LED 5.5-50W MR16 GU5.3

LEDspots MAS SLR 2 MR11 GU4

Dimensional drawing







General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime	70 %
(Nom)	
Operating and Electrical	
Input Frequency	- Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No

Product	D	С
MASTER LED 5.5-50W 2700K MR16 24D	50.2 mm	49 mm
MASTER LED 5.5-50W 2700K MR16 36D	50.2 mm	49 mm
MASTER LED 5.5-50W 3000K MR16 24D	50.2 mm	49 mm
MASTER LED 5.5-50W 3000K MR16 36D	50.2 mm	49 mm
MASTER LED 5.5-50W 4000K MR16 24D	50.2 mm	49 mm

Product	D	С
MAS LEDspotLV 3.5-20W 827 MR11 24D	35.1 mm	39.5 mm

Product	D	С
MASTER LED 3.9-35W 2700K MR16 24D	50.5 mm	50 mm
MASTER LED 3.9-35W 3000K MR16 36D	50.5 mm	50 mm
MASTER LED 4.9-50W 3000K MR16 36D	50.5 mm	50 mm
MASTER LED 4.9-50W 4000K MR16 36D	50.5 mm	50 mm

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	GU5.3	25,000 hour(s)
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	GU5.3	25,000 hour(s)
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	GU5.3	25,000 hour(s)
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	GU5.3	25,000 hour(s)
929001146808	MASTER LED 5.5-50W 4000K MR16 24D	GU5.3	25.000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	GU4	40,000 hour(s)
929003610208	MASTER LED 3.9-35W 2700K MR16 24D	GU5.3	25,000 hour(s)
929003610508	MASTER LED 3.9-35W 3000K MR16 36D	GU5.3	25,000 hour(s)
929003611008	MASTER LED 4.9-50W 3000K MR16 36D	GU5.3	25,000 hour(s)
929003611108	MASTER LED 4.9-50W 4000K MR16 36D	GU5.3	25,000 hour(s)

Light Technical

0							
			Correlated Color	Color rendering			Luminous Intensity
Order Code	Full Product Name	Beam Angle (Nom)	Temperature (Nom)	index (CRI)	Color Code	Luminous Flux	(Nom)
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	24 degree(s)	2700 K	80	827	415 lm	1,800 cd
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	36 degree(s)	2700 K	80	827	415 lm	1,000 cd
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	36 degree(s)	3000 K	80	830	425 lm	1,000 cd
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	24 degree(s)	3000 K	80	830	425 lm	1,800 cd
929001146808	MASTER LED 5.5-50W 4000K MR16 24D	24 degree(s)	4000 K	80	840	450 lm	1,800 cd
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	24 degree(s)	2700 K	80	827	200 lm	1,000 cd
929003610208	MASTER LED 3.9-35W 2700K MR16 24D	24 degree(s)	2700 K	90	927	270 lm	1,000 cd
929003610508	MASTER LED 3.9-35W 3000K MR16 36D	36 degree(s)	3000 K	90	930	280 lm	600 cd
929003611008	MASTER LED 4.9-50W 3000K MR16 36D	36 degree(s)	3000 K	90	930	425 lm	950 cd
929003611108	MASTER LED 4.9-50W 4000K MR16 36D	36 degree(s)	4000 K	90	940	430 lm	950 cd

Operating and Electrical

Operating ar				
		Line	Power	Wattage
Order Code	Full Product Name	Frequency	Consumption	Equivalent
929001145908	MASTER LED	- Hz	5.5 W	50 W
	5.5-50W 2700K			
	MR16 24D			
929001146108	MASTER LED	- Hz	5.5 W	50 W
	5.5-50W 2700K			
	MR16 36D			
929001146608	MASTER LED	- Hz	5.5 W	50 W
	5.5-50W 3000K			
	MR16 36D			
929001146708	MASTER LED	- Hz	5.5 W	50 W
	5.5-50W 3000K			
	MR16 24D			
929001146808	MASTER LED	- Hz	5.5 W	50 W
	5.5-50W 4000K			
	MR16 24D			

Temperature

		Ambient	T-Case
Order Code	Full Product Name	temperature range	Maximum (Nom)
929001145908	MASTER LED 5.5-50W 2700K	-	95 ℃
	MR16 24D		
929001146108	MASTER LED 5.5-50W 2700K	-	95 ℃
	MR16 36D		
929001146608	MASTER LED 5.5-50W 3000K	-	95 ℃
	MR16 36D		

		Ambient	T-Case
Order Code	Full Product Name	temperature range	Maximum (Nom)
929001146708	MASTER LED 5.5-50W 3000K	-	95 °C
	MR16 24D		
929001146808	MASTER LED 5.5-50W 4000K	-	95 ℃
	MR16 24D		
929003087002	MAS LEDspotLV 3.5-20W 827	-	85 °C
	MR11 24D		

		Ambient	T-Case
Order Code	Full Product Name	temperature range	Maximum (Nom)
929003610208	MASTER LED 3.9-35W 2700K	-20 to +45 °C	68 °C
	MR16 24D		
929003610508	MASTER LED 3.9-35W 3000K	-20 to +45 °C	68 °C
	MR16 36D		

		Ambient	T-Case
Order Code	Full Product Name	temperature range	Maximum (Nom)
929003611008	MASTER LED 4.9-50W 3000K MR16 36D	-20 to +45 °C	72 °C
929003611108	MASTER LED 4.9-50W 4000K MR16 36D	-20 to +45 °C	72 °C


Mechanical and Housing


Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	-	MR16
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	-	MR16
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	-	MR16
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	-	MR16
929001146808	MASTER LED 5.5-50W 4000K MR16 24D	-	MR16


Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	-	MR11
929003610208	MASTER LED 3.9-35W 2700K MR16 24D	Clear	MR16
929003610508	MASTER LED 3.9-35W 3000K MR16 36D	Clear	MR16
929003611008	MASTER LED 4.9-50W 3000K MR16 36D	Clear	MR16
929003611108	MASTER LED 4.9-50W 4000K MR16 36D	Clear	MR16


Approval and Application

• •	• •	
		Energy Consumption kWh/
Order Code	Full Product Name	1000 h
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	- kWh
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	- kWh
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	- kWh
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	- kWh
929001146808	MASTER LED 5.5-50W 4000K MR16 24D	- kWh
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	4 kWh
929003610208	MASTER LED 3.9-35W 2700K MR16 24D	-
929003610508	MASTER LED 3.9-35W 3000K MR16 36D	-
929003611008	MASTER LED 4.9-50W 3000K MR16 36D	-
929003611108	MASTER LED 4.9-50W 4000K MR16 36D	-












Accent Diagrams



Accent Diagram - MASTER LED 4.9-50W 3000K MR16 36D




Accent Diagram - MASTER LED 5.5-50W 2700K




Accent Diagram - MASTER LED 5.5-50W 2700K MR16 36D


Accent Diagrams




Accent Diagram - MASTER LED 5.5-50W 3000K MR16 36D




Accent Diagram - MASTER LED 5.5-50W 3000K MR16 24D




Accent Diagram - MASTER LED 5.5-50W 4000K MR16 24D




Accent Diagram - MASTER LED 3.9-35W 2700K MR16 24D



Accent Diagram - MASTER LED 3.9-35W 3000K MR16 36D





Accent Diagram - MAS LEDspotLV 3.5-20W 827 MR11 24D




Accent Diagram - MASTER LED 4.9-50W 4000K MR16 36D

Beam Diagrams










Beam diagram - MASTER LED 5.5-50W 2700K MR16 24D

Beam diagram - MASTER LED 5.5-50W 2700K MR16 36D

Beam diagram - MASTER LED 5.5-50W 3000K MR16 36D










Beam diagram - MASTER LED 5.5-50W 3000K MR16 24D

Beam diagram - MASTER LED 5.5-50W 4000K MR16 24D

Beam diagram - MASTER LED 4.9-50W 4000K MR16 36D








Beam diagram - MASTER LED 4.9-50W 3000K MR16 36D

Beam diagram - MASTER LED 3.9-35W 3000K

Beam diagram - MASTER LED 3.9-35W 2700K MR16 24D

Beam Diagrams



Beam diagram - MAS LEDspotLV 3.5-20W 827 MR11 24D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.