



MVP128/158 - Consistent and efficient lighting

SLS1500

SLS projectors are lightweight and compact. Ideal for outdoor lighting, they are designed for use with 1500 W metal-halide lamps or 1000 W sodium vapor lamps. They are available in two beam apertures: open and closed. A high-gloss aluminum reflector with enclosed glass front provides protection against dust. They are easy to install and deliver excellent lighting performance.

Benefits

- High-gloss aluminum reflectors, available for two different beam apertures
- Enclosed glass front that does not allow water to enter
- Wiring: flexible cable with 1.5 mm² cross-section with fiber-glass insulation
- Maintenance: easy access to equipment by releasing the cover and loosening the screws. Lamp is accessed by releasing the three stainless-steel fasteners and tilting the rim of the glass. Cleaned with a soft, clean, damp cloth with a solution of alcohol and water (50%)

Features

- Extremely robust and resistant for outdoor use
- Equipped with lamp and ballast (housing fixed to the reflector)
- Various beam aperture options to suit different needs
- Easy maintenance and access to parts

SLS1500

Application

- Sports areas
- Stadiums
- Racetracks
- Gymnasiums
- Building facades
- Monuments

Specifications

Type	MVP128
	MVP158

Power and lamp models	1 x MH / E39 / 1500 W
	1 x SON-T / E40 / 1000 W

Versions



Accessories

Ordercode 919306010831



General Information

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
919506010133	MVP128 E40 MAX1500W R-NB IP55	E40	-	-	Reflector narrow beam
919506010153	MVP158 E40 MAX1500W R-WB IP55	E40	-	-	Reflector wide beam

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
919506110121	MVP128 MH1500W-BU R-NB IP55	-	MH	1500 W	Reflector narrow beam
919506110141	MVP158 MH1500W-BU R-WB IP55	-	MH	1500 W	Reflector wide beam

SLS1500

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
919506110161	MVP128 SON-T1000W R- NB IP55	-	SON-T	1000 W	Reflector narrow beam

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
919506110171	MVP158 SON-T1000W R- WB IP55	-	SON-T	1000 W	Reflector wide beam

