




OptiFlood – compact and complete solution

OptiFlood Mini MVP504

Philips has a long tradition of excellence in environmentally friendly asymmetric floodlighting systems for sports and general area lighting as well as architectural applications. OptiFlood's extremely efficient, best-in-class optical system provides an accurately controlled light distribution – total light cut-off above the horizontal and a peak beam intensity at high angles – keeping obtrusive light to a minimum. Both the MVP504 and MVP506 versions are available with two types of reflector – asymmetric or road-lighting POT optics – for flexibility in application. They can also accommodate CosmoPolis metal-halide lamps for good color rendering, high-pressure sodium lamps for economical operation, and MASTERColour CDM Elite MW lamps for highly efficient lighting with longer-lasting white light. OptiFlood is also available in a LED version (BVP506). With its compact shape and aesthetically pleasing design, OptiFlood can be used in applications where design and appearance are just as important as technical performance. In the design, attention has also been focused on the detailing. This has led to integrated 'hidden' hinges, angle adjustment designed as part of the body and a mounting bracket angled to allow more aesthetic integration onto columns.

Faydaları

- Environment-friendly asymmetrical floodlighting systems for general area lighting as well as security and industrial area lighting
- Best-in-class optical system for accurately controlled light distribution to prevent uncontrolled stray and spill light
- Compact shape and pleasing design allows OptiFlood to be used in settings where design and appearance are just as important as technical performance

OptiFlood Mini MVP504

Özellikler

- Kompakt görünüm ve zevkli tasarım
- İki tür reflektör – asimetrik veya yol aydınlatma POT optikleri
- CosmoPolis metal halojenür ampuller, yüksek basınçlı sodyum lambalar ve MASTERColour CDM Elite MW ampuller bulundurabilir
- Ayrıca LED sürümü de mevcuttur

Uygulama

- Genel alan aydınlatması
- Araç park yerleri
- Mimari ışıklandırma

Versions



ÜRÜN BİLGİLERİ

Ön kapak iki paslanmaz klipsle yerine sabitlenmiştir ve bir tornavidayla kolayca yerinden çıkarılabilir



Açıldığında iyice geriye doğru çekilebilen ön kapak, tertibat ve ampul bölmesine tam erişime olanak tanır



Açıldığında iyice geriye doğru çekilebilen ön kapak, tertibat ve ampul bölmesine tam erişime olanak tanır




Ön kapak tam açıldığında, tüm komponentlere mükemmel erişim olanağı tanır



OptiFlood Mini MVP504

ÜRÜN BİLGİLERİ



Konektör



CosmoPolis optik



Birden çok ufak gözden oluşan yol
aydınlatma POT optiği



Birden çok ufak gözden oluşan yol
aydınlatma POT optiği



Asimetrik optik



Asimetrik optik

Onay ve Uygulama

Mekanik çarpışma koruma kodu IK08

Genel Bilgiler

CE işareti CE mark

Optik kapak/lens türü GC

ENEC işareti -

Tertibat EB

Işık kaynağı sayısı 1

Ürün Ailesi Kodu MVP504

Genel Bilgiler

OptiFlood Mini MVP504

Order Code	Full Product Name	Işık kaynağı rengi	Lamba ailesi kodu	Lamba gücü	Optik sistem türü
29270100	MVP504 CDM-TD70W/942 EB I A	942 nötr beyaz	CDM-TD	70 W	Asymmetrical
29273200	MVP504 CDM-TD150W/942 EB I A	942 nötr beyaz	CDM-TD	150 W	Asymmetrical
29274900	MVP504 CDO-TT70W K EB I A	-	CDO-TT	70 W	Asymmetrical
29277000	MVP504 CPO-TW45W K EB I A	-	CPO-TW	45 W	Asymmetrical
29278700	MVP504 CPO-TW60W K EB I A	-	CPO-TW	60 W	Asymmetrical
29279400	MVP504 CPO-TW90W K EB I A	-	CPO-TW	90 W	Asymmetrical
29289300	MVP504 CDM-TD150W/942 EB II A	942 nötr beyaz	CDM-TD	150 W	Asymmetrical
29293000	MVP504 CPO-TW45W K EB II A	-	CPO-TW	45 W	Asymmetrical
29295400	MVP504 CPO-TW90W K EB II A	-	CPO-TW	90 W	Asymmetrical
29302900	MVP504 CDM-TD70W/942 EB I A GR	942 nötr beyaz	CDM-TD	70 W	Asymmetrical
29305000	MVP504 CDM-TD150W/942 EB I A GR	942 nötr beyaz	CDM-TD	150 W	Asymmetrical
29306700	MVP504 CDO-TT70W K EB I A GR	-	CDO-TT	70 W	Asymmetrical
29309800	MVP504 CPO-TW45W K EB I A GR	-	CPO-TW	45 W	Asymmetrical
29310400	MVP504 CPO-TW60W K EB I A GR	-	CPO-TW	60 W	Asymmetrical
29311100	MVP504 CPO-TW90W K EB I A GR	-	CPO-TW	90 W	Asymmetrical
29318000	MVP504 CDM-TD70W/942 EB II A GR	942 nötr beyaz	CDM-TD	70 W	Asymmetrical
29321000	MVP504 CDM-TD150W/942 EB II A GR	942 nötr beyaz	CDM-TD	150 W	Asymmetrical
29322700	MVP504 CDO-TT70W K EB II A GR	-	CDO-TT	70 W	Asymmetrical

Order Code	Full Product Name	Işık kaynağı rengi	Lamba ailesi kodu	Lamba gücü	Optik sistem türü
29325800	MVP504 CPO-TW45W K EB II A GR	-	CPO-TW	45 W	Asymmetrical
29326500	MVP504 CPO-TW60W K EB II A GR	-	CPO-TW	60 W	Asymmetrical
29327200	MVP504 CPO-TW90W K EB II A GR	-	CPO-TW	90 W	Asymmetrical
29334000	MVP504 CDM-T35W/842 EB I TP-S	842 nötr beyaz	CDM-T	35 W	Open T-POT small
29337100	MVP504 CDM-T70W/942 EB I TP-S	942 nötr beyaz	CDM-T	70 W	Open T-POT small
29340100	MVP504 CPO-TW45W K EB I	-	CPO-TW	45 W	Optic for CosmoPolis lamp
29341800	MVP504 CPO-TW60W K EB I	-	CPO-TW	60 W	Optic for CosmoPolis lamp
29342500	MVP504 CPO-TW90W K EB I	-	CPO-TW	90 W	Optic for CosmoPolis lamp
29344900	MVP504 CDM-T35W/842 EB II TP-S	842 nötr beyaz	CDM-T	35 W	Open T-POT small
29351700	MVP504 CPO-TW60W K EB II	-	CPO-TW	60 W	Optic for CosmoPolis lamp
29354800	MVP504 CDM-T35W/842 EB I TP-S GR	842 nötr beyaz	CDM-T	35 W	Open T-POT small
29361600	MVP504 CPO-TW60W K EB I GR	-	CPO-TW	60 W	Optic for CosmoPolis lamp
29362300	MVP504 CPO-TW90W K EB I GR	-	CPO-TW	90 W	Optic for CosmoPolis lamp
29364700	MVP504 CDM-T35W/842 EB II TP-S GR	842 nötr beyaz	CDM-T	35 W	Open T-POT small
29367800	MVP504 CDM-T70W/942 EB II TP-S GR	942 nötr beyaz	CDM-T	70 W	Open T-POT small
29370800	MVP504 CPO-TW45W K EB II GR	-	CPO-TW	45 W	Optic for CosmoPolis lamp
29371500	MVP504 CPO-TW60W K EB II GR	-	CPO-TW	60 W	Optic for CosmoPolis lamp

Mekanik Ayrıntılar ve Muhafaza

Order Code	Full Product Name	Renk
29270100	MVP504 CDM-TD70W/942 EB I A	-
29273200	MVP504 CDM-TD150W/942 EB I A	-
29274900	MVP504 CDO-TT70W K EB I A	-
29277000	MVP504 CPO-TW45W K EB I A	-
29278700	MVP504 CPO-TW60W K EB I A	-
29279400	MVP504 CPO-TW90W K EB I A	-
29289300	MVP504 CDM-TD150W/942 EB II A	-
29293000	MVP504 CPO-TW45W K EB II A	-
29295400	MVP504 CPO-TW90W K EB II A	-

Order Code	Full Product Name	Renk
29302900	MVP504 CDM-TD70W/942 EB I A GR	Gray
29305000	MVP504 CDM-TD150W/942 EB I A GR	Gray
29306700	MVP504 CDO-TT70W K EB I A GR	Gray
29309800	MVP504 CPO-TW45W K EB I A GR	Gray
29310400	MVP504 CPO-TW60W K EB I A GR	Gray
29311100	MVP504 CPO-TW90W K EB I A GR	Gray
29318000	MVP504 CDM-TD70W/942 EB II A GR	Gray
29321000	MVP504 CDM-TD150W/942 EB II A GR	Gray
29322700	MVP504 CDO-TT70W K EB II A GR	Gray

OptiFlood Mini MVP504

Order Code	Full Product Name	Renk
29325800	MVP504 CPO-TW45W K EB II A GR	Gray
29326500	MVP504 CPO-TW60W K EB II A GR	Gray
29327200	MVP504 CPO-TW90W K EB II A GR	Gray
29334000	MVP504 CDM-T35W/842 EB I TP-S	-
29337100	MVP504 CDM-T70W/942 EB I TP-S	-
29340100	MVP504 CPO-TW45W K EB I	-
29341800	MVP504 CPO-TW60W K EB I	-
29342500	MVP504 CPO-TW90W K EB I	-
29344900	MVP504 CDM-T35W/842 EB II TP-S	-

Order Code	Full Product Name	Renk
29351700	MVP504 CPO-TW60W K EB II	-
29354800	MVP504 CDM-T35W/842 EB I TP-S GR	Gray
29361600	MVP504 CPO-TW60W K EB I GR	Gray
29362300	MVP504 CPO-TW90W K EB I GR	Gray
29364700	MVP504 CDM-T35W/842 EB II TP-S GR	Gray
29367800	MVP504 CDM-T70W/942 EB II TP-S GR	Gray
29370800	MVP504 CPO-TW45W K EB II GR	Gray
29371500	MVP504 CPO-TW60W K EB II GR	Gray

