



Zadora – free to create

Zadora, adjustable

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Benefits

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Adjustable downlights with beam widths of 8°, 24°, 36° or 60° and 30° orientation from the vertical to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Features

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths
- Also available in complete, ready-to-install kit versions

Application

- Retail
- Offices

Specifications

Type	QBD570	Lamp beam angle	MASTERLine 25°, 40°
Light source	Halogen: <ul style="list-style-type: none">- 1 x MASTERLine ES / GU5.3 / 45 W- 1 x Brilliantline Dichroic / GU4 / 20, 35 W- 1 x Twistline Dichro / GZ10 / 50 W	Lamp included	No (optional)
		Lamp position	Vertical
		Transformer	Electronic (ET)

Zadora, adjustable

Color	Grey (GR)	Material	Die-cast aluminum and steel
	White (WH)	Installation	Fixation by means of spring fasteners
	Black (BK)	Maintenance	Direct lamp access
	Anthracite (ANT)	Remarks	Bracket (BR) installed to ensure a safe distance between luminaire and ceiling
	Aluminum (ALU)		Dedicated ready to install versions available (K), downlight, lamp and electronic transformer
	Matt finishing (MAT)		
	Chrome (CR)	Main applications	Office, retail
	Gold (GO)		

Dimensional drawing

Zadora Adjustable QBD570

Approval and Application

Mech. impact protection code	IK00
Ingress protection code	IP20

Operating and Electrical

Input Voltage	230
----------------------	-----

General Information

Beam angle of light source	40
Cap-Base	GZ10
CE mark	CE mark
Protection class IEC	Safety class II (II)
ENEC mark	-
Flammability mark	F
Gear	-
Glow-wire test	850/5
Kombipack	Lamp(s) included
Lamp family code	HAL-R
Lamp power	50
Number of light sources	1
Product Family Code	QBD570

General Information

order code	Color
57312000	White
57315100	Aluminum

Zadora, adjustable

