



Zadora – free to create

Zadora, adjustable

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Benefits

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Adjustable downlights with beam widths of 8°, 24°, 36° or 60° and 30° orientation from the vertical to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Features

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths
- Also available in complete, ready-to-install kit versions

Application

- Retail
- Offices

Specifications

Type	QBD570	Light source	Halogen:
			- 1 x MASTERLine ES / GU5.3 / 45 W
			- 1 x Brilliantline Dichroic / GU4 / 20, 35 W
			- 1 x Twistline Dichro / GZ10 / 50 W

Zadora, adjustable

Lamp beam angle	MASTERLine 25°, 40°
Lamp included	No (optional)
Lamp position	Vertical
Transformer	Electronic (ET)
Color	Grey (GR)
	White (WH)
	Black (BK)
	Anthracite (ANT)
	Aluminum (ALU)
	Matt finishing (MAT)
	Chrome (CR)
	Gold (GO)

Material	Die-cast aluminum and steel
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access
Remarks	Bracket (BR) installed to ensure a safe distance between luminaire and ceiling
	Dedicated ready to install versions available (K), downlight, lamp and electronic transformer
Main applications	Office, retail

Versions



Zadora QBD570 adjustable
downlight with halogen lamp



Zadora QBD570 adjustable
downlight with halogen lamp

Application conditions	
Ambient temperature range	-10 to +35 °C
Approval and application	
Mech. impact protection code	IK00
Ingress protection code	IP20
Operating and electrical	
Input Voltage	12 V
General information	
Cap-Base	E27
Protection class IEC	Safety class III
Gear	-
Lamp power	45 W
Number of light sources	1 pc

Mechanical and housing

Order Code	Full Product Name	Color
910502538418	QBD570 1xHAL-MR50-45W 12V BR WH	White
910502538718	QBD570 1xHAL-MR50-45W 12V BR ALU	Aluminum

Zadora, adjustable

