



Smart Halogen Downlight – a reliable way to make your merchandise stand out

Smart Halogen Downlight QBS020

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

Benefits

- Affordable yet highly effective accent-lighting solution
- Safe and durable
- Wide choice for customers; contemporary sophistication

Features

- Robust housing
- Different shapes to suit different functions
- Professional finish
- Good-quality clips for easy installation

Smart Halogen Downlight QBS020

Application

- Retail – sales areas, shop windows
- Offices – exhibition and highlight areas
- Hospitality and cruise ships – corridors, service areas, reception areas, lobbies, lounges, restaurants, cabins
- Healthcare – corridors, reception areas, waiting areas
- Airports – arrival/departure halls, corridors, waiting areas, service desks, shops

Specifications

Type	Die-cast aluminum versions and for MR11 lamp types: <ul style="list-style-type: none">- QBS020, 022: fixed- QBS021: adjustable Die-cast aluminum versions and for MR16 lamp types: <ul style="list-style-type: none">- QBS023, 026, QBS040~046: fixed- QBS024, 025, 027~029, QBS047: adjustable Cast aluminum versions and for MR16 lamp types: <ul style="list-style-type: none">- QBS030, 032: fixed- QBS031: cardanic	Lamp position	Vertical
Light source	Halogen: <ul style="list-style-type: none">- 1 x ESSENTIAL 1CT / GU4 / 20, 35 W- 1 x ESSENTIAL Closed 1CT / GU5.3 / 20, 50 W	Light distribution	Direct (D)
Lamp beam angle	30 , 36°	Transformer	12 V (not included)
Lamp included	No	Material	QBS020~029, QBS040~047 versions: <ul style="list-style-type: none">- Die-cast aluminum QBS030~032 versions: <ul style="list-style-type: none">- Cast aluminum
		Color	QBS020~029, QBS040~047 versions: <ul style="list-style-type: none">- White and grey QBS030~032 versions: <ul style="list-style-type: none">- Silver
		Installation	Fixation by means of spring fasteners
		Maintenance	Direct lamp access
		Main applications	Retail, fashion, hospitality

