



# QBS105

## QBS105

Standard professional recessed. Extra-Low Voltage downlights for dichroic halogen lamp.

### Features

- Premium die cast aluminum body not only gives a very light weight but also improves heat ventilation to reduce ceiling board from dust.
- Interchangeable optic attachments can meet most different lighting requirements. Do not need to change the whole luminaire but just change the different attachment.
- The special designed fixed clips allow you to adjust to suit different ceiling board thickness ranging from 1 mm to 32 mm.
- Specially designed aluminum lamp holder sinker to diverge the temperature of lamp away from the lamp base for a longer life.
- The decorative ring can be changed to different color to meet the interior design requirements.

### Application

- Representative offices
- Conference rooms
- Small offices
- General open plan offices
- Recreation areas (sport halls, restaurants, cafeterias)
- Department stores, fashion shops
- Small independent food/non-food shops
- High-end fashion shops, boutiques

## QBS105

### Versions

