



Zadora – free to create

Zadora, fixed

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Výhody

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Fixed downlights with beam widths of 8°, 24°, 36° or 60° to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Vlastnosti

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths

Aplikace

- Office
- Retail

Zadora, fixed

Versions



Pevné svítidlo Zadora QBS570 s halogenovou žárovkou



Pevné svítidlo Zadora QBS570 s halogenovou žárovkou



Pevné svítidlo Zadora QBS570 s halogenovou žárovkou



Pevné svítidlo Zadora QBS570 s halogenovou žárovkou

Approval and Application

IP kód	IP20
--------	------

Operating and Electrical

Vstupní napětí	12 V
----------------	------

General Information

Patice	GU5.3
Značka CE	CE mark
Třída ochrany IEC	Bezpečnostní třída II
Značka ENEC	-
Značka hořlavosti	F
Předřadník	-
Test žhavým drátem	Teplota 850 °C, doba 5 s
Kombipack	K
Kód řady zdroje	HAL-MR50
Příkon zdroje	45 W
Počet světelných zdrojů	1

Mechanical and Housing

Order Code	Full Product Name	Barva
57320599	QBS570 1xHAL-MR50-45W 12V BR WH	WH
57321299	QBS570 1xHAL-MR50-45W 12V BR CR	Chrome
57323699	QBS570 1xHAL-MR50-45W 12V BR ALU	ALU
57325099	QBS570 1xHAL-MR50-45W 12V BR MAT	MAT

Zadora, fixed

